



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'HSTT38-C4'

Your search criteria matched only one product, shown below

HSTT38-C4



Flexible Ployolefin DRY-SHRINKTMHeat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 275°F (-55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

Part Number	HSTT38C4
RoHS Compliance Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink
Material	Polyolefin cross-linked
Color	Yellow
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 1
UL Recognized	E122770
CE Compliant	No
CE Marking	No
Flammability Rating	Flame Retardant
Length Per Reel (ft.)	100
Length Per Reel (m)	30.5
Max. Recovered I.D. (In.)	.187
Max. Recovered I.D. (mm)	4.8
Min. Expanded I.D. (In.)	.375
Min. Expanded I.D. (mm)	9.5
Nominal Diameter / Size	.375
Nominal Recovered Wall Thickness (In.)	.025
Nominal Recovered Wall Thickness (mm)	.6
Pricing Description	Heat Shrink Thin, .38"(9.5mm) Dia, Yellow
Shrink Ratio	2:1
Temperature Range	-67°F to 275°F (55°C to 135°C)
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.