



Series 800 Mighty Mouse UN Mating Thread Plug

800-006 Thru 800-009 Ordering Information



Glenair's Smallest Mighty Mouse Connector has compact size and rugged design for hostile environments. UN mating thread. Connector shells are machined aluminum or stainless steel. Supplied with crimp contacts, packaged separately. Terminate contacts with standard M22520 tools. Metal clips inside the connector body lock contact into place. Contacts are removable. Fluorosilicone seals and rear grommet protect connector from water ingress. Choose hex or knurled coupling nut. Terminate cable shield directly to connector body with Band-Master™ ATS strap, or choose rear accessory thread to attach optional cable clamp or backshell. Available in shell sizes 5 through 12 in 36 contact arrangements.

C

How To Order

Sample Part Number		800-006	-06	M	6-7	P	N
Series (See Table I)	800-006 = Hex Plug with Banding Platform 800-007 = Hex Plug with Accessory Thread 800-008 = Plug with Band Platform 800-009 = Plug with Accessory Thread						
Shell Style	-06 = Standard Coupling Nut -16 = Coupling Nut with Anti-Decoupling Wave Spring						
Shell Material and Finish	C = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant M = Aluminum / Electroless Nickel RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate MT = Aluminum / Nickel-PTFE RoHS Compliant Z1 = Stainless Steel / Passivated RoHS Compliant						
Shell Size - Insert Arrangement	See Contact Arrangements page C-2						
Contact Type	Connector supplied with crimp contacts P = Pin S = Socket	Connector supplied without contacts A = Pin Connector B = Socket Connector	Connector supplied with 30 AWG crimp contacts G = Pin H = Socket				
Shell Key Positions (See Table II)	N = Normal X = Pos. X Y = Pos. Y Z = Pos. Z						

Table I: Series

800-006 Hex Plug with Banding Platform	800-007 Hex Plug with Accessory Thread	800-008 Knurled Round Plug with Band Platform	800-009 Knurled Round Plug with Accessory Thread

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[800-008-06M8-13PN](#) [800-008-16M6-4PN](#) [800-006-06M10-26PN](#) [800-006-06M10-26SN](#) [800-006-06M5-3PN](#) [800-006-06M5-3SN](#) [800-006-06M6-4PN](#) [800-006-06M6-4SN](#) [800-006-06M6-7PN](#) [800-006-06M6-7SN](#) [800-006-06M7-10SN](#) [800-006-06M8-13PN](#) [800-006-06M8-13SN](#) [800-006-06M9-19PN](#) [800-006-06M9-19SN](#) [800-006-06NF6-4PN](#) [800-006-06NF6-7PN](#) [800-006-06Z16-4SN](#) [800-006-06Z16-7PN](#) [800-006-06Z16-7SN](#) [800-006-06Z19-19SN](#) [800-006-16M12-37PN](#) [800-006-16M12-37SN](#) [800-006-16M9-19SN](#) [800-006-16Z16-4PN](#) [800-006-16Z16-4SN](#) [800-006-16Z16-7SN](#) [800-006-16Z19-19SN](#) [800-008-06M10-26PN](#) [800-008-06M10-26SN](#) [800-008-06M12-37PN](#) [800-008-06M12-37SN](#) [800-008-06M5-3PN](#) [800-008-06M5-3SN](#) [800-008-06M6-4PN](#) [800-008-06M6-4SN](#) [800-008-06M6-7PN](#) [800-008-06M6-7SN](#) [800-008-06M7-10PN](#) [800-008-06M7-10SN](#) [800-008-06M8-13SN](#) [800-008-06M9-19PN](#) [800-008-06M9-19SN](#) [800-008-06NF6-4PN](#) [800-008-06NF6-7PN](#) [800-008-06NF9-19PN](#) [800-008-06NF9-19SN](#) [800-008-16M6-7PN](#) [800-008-16M6-7SN](#) [800-008-16Z16-4PN](#) [800-008-16Z16-7PN](#) [800-008-16Z19-19SN](#) [800-008-16ZB6-4PN](#) [800-008-16ZN9-19SN](#) [800-009-06M10-26PN](#) [800-009-06M10-26SN](#) [800-009-06M12-37SN](#) [800-009-06M5-3PN](#) [800-009-06M5-3SN](#) [800-009-06M6-4PN](#) [800-009-06M6-4SN](#) [800-009-06M6-7PN](#) [800-009-06M7-10PN](#) [800-009-06M7-10SN](#) [800-009-06M8-13PN](#) [800-009-06M8-13SN](#) [800-009-06M9-19PN](#) [800-009-06Z16-7SN](#) [800-009-16M12-37PN](#) [800-009-16M12-37SN](#) [800-009-16M6-7PN](#) [800-009-16M6-7SN](#) [800-009-16M9-19SN](#) [800-009-16NF12-37PN](#) [800-009-16NF15-85PN](#) [800-009-16NF6-7SN](#) [800-006-06ZN6-7SN](#) [800-006-06M7-10PN](#) [800-006-06Z15-3SN](#) [800-006-06Z17-10SN](#) [800-006-06ZNU7-10PN](#) [800-006-06ZNU7-10PZ](#) [800-006-06ZNU7-10SN](#) [800-006-06ZNU7-10SZ](#) [800-007-16Z15-3SN](#) [800-008-06NF5-3PN](#) [800-008-06ZNU6-7PZ](#) [800-008-16M5-3PZ](#) [800-008-16M6-4PX](#) [800-008-16ZR6-7SN](#) [800-009-06NF12-2PN](#) [800-009-06NF5-3SN](#) [800-009-06NF7-10SN](#) [800-009-06ZN7-10PN](#) [800-009-16NF7-10SN](#) [800-009-16NF8-13PN](#) [800-009-16NF9-19SN](#) [800-009-16ZB12-37SN](#) [800-007-06NF6-7PN](#) [800-006-06NF8-13SN](#)