










REV.	DATE	ECR NO.	DESCRIPTION
NC	11/23/08	—	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMS.



NOTE:
1. CONTACT PIN TO SOLDER.



9	HEX NUT	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8	WASHER	BRASS	GOLD	1		DRAWN	GRS	11/23/08							
7	GASKET	SILICONE	RED	1		CHECKED									
6	TOP HAT	BRASS	GOLD	1						PART DESCRIPTION SMB CLAMP PLUG (FOR RG-174/U, 188A/U 316/U CABLE)					
5	WASHER	BRASS	GOLD	1											
4	CONTACT PIN	BER. COPPER	GOLD	1											
3	INSULATOR	PTFE	NATURAL	1						PART NO. 142118					
2	SHELL	BRASS	GOLD	1											
1	BODY	BRASS	GOLD	1											
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE C:/142/142118.DWG		DWG. NO. 142118.DWG		REV. NC	SIZE A	SCALE NA				