




---

**J**

## Slide

- 



# V Series Power & Line Voltage Select Slide Switches

## SWITCH FUNCTION


| NO. POLES | MODEL NO. | SWITCH FUNCTION | SCHEMATIC | AVAILABLE MOUNTING STYLES |
|-----------|-----------|-----------------|-----------|---------------------------|
| SP        | V701      | SPST            | 1A 1      | ALL                       |
|           | V702      | SPDT            | 1A 1 1B   | ALL                       |

All models    with all options.  
Contacts make on side actuator thrown.

| NO. POLES | MODEL NO. | SWITCH FUNCTION | SCHEMATIC          | AVAILABLE MOUNTING STYLES |
|-----------|-----------|-----------------|--------------------|---------------------------|
| DP        | V801      | DPST            | 1A 1<br>2A 2       | ALL                       |
|           | V802      | DPDT            | 1A 1 1B<br>2A 2 2B | ALL                       |


## ACTUATOR

**12** SCREWDRIVER SLOT  
WITH MARKING




Actuator color is red with white  
115V-230V markings (std.).

**01** .290" HIGH




Actuator color is black.

**02** .290" HIGH  
WITH MARKINGS




markings are reversed on V702  
and V802 models. Actuator color  
is black with white markings (std.).

**13** SCREWDRIVER SLOT  
NO MARKING



Actuator color is red.

**14** SCREWDRIVER SLOT  
WITH MARKINGS




Markings are reversed on  
V702 and V802 models.  
Actuator color is red with  
white markings (std.). **Note:** Orientation of  
actuator markings  
and terminals.

## MOUNTING STYLE


**SS** PANEL WITH MOUNTING EARS



V80212SS05Q  
DPDT



### PANEL MOUNTING




**AVAILABLE WITH:**  
**Models:** All.  
**Terminations:** 02 and 05

**MA** RIGHT ANGLE, PC THRU-HOLE



V80212MA08Q  
Horizontal Actuation  
DPDT




### AVAILABLE WITH:

**Models:** All  
**Terminations:** 08

### PC MOUNTING

PC mount, side actuated.  
For mounting information,  
see TERMINATIONS section, page J-35.



Third Angle  
Projection


Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

**C&K**

# V Series Power & Line Voltage Select Slide Switches

## MOUNTING STYLE

### MS PC THRU-HOLE



#### AVAILABLE WITH:

All models with 02 terminations

#### PC MOUNTING


PC mount, top actuated.  
For mounting information,  
see TERMINATIONS section, page J-35.




V80212MS02Q

DPDT

### SL RIGHT ANGLE PANEL WITH MOUNTING EARS



#### PANEL MOUNTING





#### AVAILABLE WITH:

All models with 08 terminations




V80213SL08Q  
Horizontal Actuation


DPDT



### S2 SNAP-IN PANEL MOUNT



#### PANEL MOUNTING



#### Panel thickness:

.020-.200 THK.  
(0,50) (5,08)

#### AVAILABLE WITH:

All models with 02 &  
05 terminations



V80212S205Q

DPDT




Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

**C&K**


# V Series Power & Line Voltage Select Slide Switches

## TERMINATIONS


### 05 QUICK CONNECT



### 02 PC THRU-HOLE




#### PC MOUNTING




MS, SS Mounting Styles.

### 08 PC THRU-HOLE



Not available with 'MS, SS or S2' mounting styles.

#### PC MOUNTING



MA, SL Mounting Styles.

## CONTACT MATERIAL

| OPTION CODE | CONTACT MATERIAL    | RATINGS |                                                                                                           |
|-------------|---------------------|---------|-----------------------------------------------------------------------------------------------------------|
| Q           | SILVER <sup>1</sup> | POWER   | 10.1 AMPS @ 125 V AC; 4 AMPS @ 28 V DC; 5 AMPS @ 250 V AC (UL/CSA); 2.0 (0.5) AMPS @ 250 V AC, T85 (VDE). |

\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

<sup>1</sup> CONTACTS & TERMINALS: Copper, silver plated (standard with all termination options).


All models with all options. V70X and V80X models .

**NOTE:** Any models supplied with Q contact material are RoHS compliant.

## SEAL

**NONE** NO SEAL

**E** EPOXY SEAL



**C&K**



Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

[www.ck-components.com](http://www.ck-components.com)