





NOTES:

1. MATERIAL:

HOUSING : POLYPROPYLENE

FLAMMABILITY RATING: UL94 HB, UL FILE NO. E216959

TEMPERATURE RANGE: -10°C TO +100°C

RIVETS: BRASS, NICKLE PLATED.

SPRING: SPRING STEEL, NICKLE PLATED.


CONTACT RESISTANCE: UNDER 50m Ω FOR ± CONTACTS PER EIA-540J000

ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT. ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
02/22/13	A	UPDATED TO "ROHS 2 COMPLIANT"	T.B.	B.S.	



Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title FOUR "N" CELL HOLDER		
Angular ± 3°	Date 02/22/13	Drawing Number BH4NL	