







REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:
Insulator Material: PBT, UL 94V-0
Contact Plating: TIN, 80-100 μ "
Contact Material: Brass

Current Rating : 1A AC,DC
Contact Resistance: 20M Ω Max.
Dielectric Withstanding: AC 500V
Insulator Resistance: 1000M Ω Min.
Operating Temp.: -40°C~+105°C



NUMBER OF POSITIONS	DIMENSIONS	
	A	B
06	4.00	21.60
08	6.00	23.60
10	8.00	25.60
12	10.00	27.60
14	12.00	29.60
16	14.00	31.60
20	18.00	35.60
24	22.00	39.60
26	24.00	41.60
30	28.00	45.60
34	32.00	49.60
40	38.00	55.60
44	42.00	59.60
50	48.00	65.60
60	58.00	75.60



UNLESS TOLERANCE		DRAW	BY	CnC Tech,LLC			
GENERAL	ANGLE	DESIGN	BY				
X. ± 0.30	X.° ± 3.0°	CHECK	BY				
.X ± 0.20	.X° ± 2.0°	APPROVE	BY				
.XX ± 0.15	.XX° ± 1.0°	Part NO. 3110-XX-003-11-99					
.XXX ± 0.08	.XXX ± 0.5°						
SCALE		SHEET	UNIT	DRAW NO:			
1:1		1/1	MM				
REV: A							