

Pelican M10 8040

www.pelicanproducts.us



M10 8040 Flashlight

The 8040 Flashlight uses a high-pressure Xenon fired lamp module that produces a powerful, bright, high intensity light. Unlike other flashlights that project a broad yellow beam, the M10 produces a tight white pre-focused beam. It comes with a polarity guard tray that makes operating the flashlight impossible if cells are inverted and prevents dangerous outgassing. The light weight Xenon body with sure-grip sheath resists chemicals and prevents slippage. The push button switch operates easily, even when wearing thick gloves. The M10 8040 is built tough to withstand the hard knocks that come in the plant, around the beat or on patrol. Powered by 4 C alkaline cells.

Minimum Pack 1 ea.

Packaged Weight: 10.7 oz.

M10 8040 Flashlight Specifications

	High	
LIGHT SOURCE	Xenon	
BATTERIES	4 C Alkaline (Not included)	
CHARGE TIME	N/A	
VOLTAGE	6	
LENGTH	11.25" (28.6 cm)	
WEIGHT w/ BATTERIES	18.4 oz. (0.52 kg)	
WEIGHT w/o BATTERIES	11.04 oz. (0.31 kg)	

	FL 1 STANDARD	High	
LIGHT OUTPUT		67 LUMENS	
RUNTIME (hours/min)		5h 15m	
BEAM DISTANCE (meters)		198m	
PEAK BEAM INTENSITY (candela)		9820cd	

M10 8040 Flashlight Configurations

Cat. #	Description
8040	M10 8040 Flashlight (Boxed)

NSN List

NSN #	Description
6230-01-514-1518	8040 M10
6230-01-513-4994	M10 ALKALINE 4C

M10 8040 Flashlight Accessories

Cat. #	Description
8044	M10 8040 Lamp Module
8057	Cordura® Holster
8052OR	Traffic Wand (Orange)
8052YW	Traffic Wand (Yellow)

M10 8040 Flashlight Approvals

	Class I, Div. 2 Gp. ABCD T3C; Class II Div. 2 Gp. FG -35° TO +40°C
	Class I, Div. 2 Gp. ABCD T3A; Class II III Div. 2 Gp. FG T4
	10C-649-0
	Ex ib e IIC T3 IP50 IEC Ex TSA06.0021X