

# IT 3057-A Cable Clamp

**Mod. Code Options**  
See Table II


**IT**

**3057-16A**

**F11**

**MIL-DTL-26482 Serie I  
Accessory**

**Finish Options**  
See Table II



**TABLE II: MODIFICATION CODES**

| Shell Finish<br>(Omit for Standard Cad/Olive Drab Finish) |
|-----------------------------------------------------------|
| <b>F6</b> - Black Electrodeposited Paint (RoHs)           |
| <b>F7</b> - Black Zinc Nickel (RoHs)                      |
| <b>F11</b> - Electroless Nickel (RoHs)                    |
| <b>MB</b> - Marine Bronze (RoHs)                          |

## Application Notes

General duty cable clamp suitable for jacketed cable or wires protected by tubing.

**TABLE I: DIMENSIONS**

| GLENAIR P/N  | Shell size | Sleeve to use | ØA | ØB   | C    | F<br>Thread in inches | L    |
|--------------|------------|---------------|----|------|------|-----------------------|------|
| IT3057 - 3A  | 8          | IT3420 - 3    | 18 | 6.8  | 10.2 | 0.5000 - 28UNEF       | 20.6 |
| IT3057 - 4A  | 10         | IT3420 - 4    | 25 | 8.2  | 10.2 | 0.6250 - 24UNEF       | 21.0 |
| IT3057 - 6A  | 12         | IT3420 - 6    | 27 | 11.2 | 10.2 | 0.7500 - 20UNEF       | 22.2 |
| IT3057 - 8A  | 14         | IT3420 - 8    | 28 | 14.2 | 10.2 | 0.8750 - 20UNEF       | 24.0 |
| IT3057 - 10A | 16         | IT3420 - 10   | 33 | 16.0 | 10.2 | 1.0000 - 20UNEF       | 28.5 |
| IT3057 - 12A | 18         | IT3420 - 12   | 35 | 19.0 | 10.2 | 1.1875 - 18NEF        | 24.0 |
| IT3057 - 12A | 20         | IT3420 - 12   | 35 | 19.0 | 10.2 | 1.1875 - 18NEF        | 24.0 |
| IT3057 - 16A | 22         | IT3420 - 16   | 43 | 23.8 | 10.5 | 1.4375 - 18NEF        | 26.0 |
| IT3057 - 16A | 24         | IT3420 - 16   | 43 | 23.8 | 10.5 | 1.4375 - 18NEF        | 26.0 |