





REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	-	INITIAL RELEASE



RECOMMENDED  
CABLE STRIPPING DIM'S



8			
7			
6			
5	FERRULE	COPPER	NICKEL
4	CONTACT PIN	PHOS. BRONZE	GOLD
3	INSULATOR	PTFE	NATURAL
2	BODY	BRASS	NICKEL
1	HOUSING	BRASS	NICKEL
	DESCRIPTION	MATERIAL	FINISH
			QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:  
0.5 - 8mm  $\pm$  0.20mm  
8 - 30mm  $\pm$  0.40mm  
30 - 120mm  $\pm$  0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:  
.020 - .315 =  $\pm$  0.007"  
.315 - 1.180 =  $\pm$  0.015"  
1.180 - 4.724 =  $\pm$  0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN GRS	02/03/09
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/122/122124.DWG

<h1>Amphenol Connex</h1>				
PART DESCRIPTION <b>TNC CRIMP JACK</b>				
PART NO. <b>122124</b>				
DWG. NO.	122124.DWG	REV.	NC	SCALE NA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122124](#)