

NOTES:
1. IDENTIFICATION: 1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19
208V / 30A / SINGLE-PHASE POU

2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS




4. UL® & c-UL® LISTED 1950.

6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

Technical drawing of the HB0B1L4BT08W power strip. The drawing includes the following dimensions and features:

- Dimensions:**
 - Overall length: 18.9 [480.1]
 - Length to last outlet: 17.0 [431.8]
 - Width of mounting bracket: 1.85 [47.0]
 - Height of mounting bracket: 1.72 [43.7]
- Features:**
 - 15A THERMAL BREAKER (4 PLACES)
 - 10 FOOT INLET POWER CORD
- Notes:**
 - 7. MAXIMUM AVAILABLE LENGTH
 - 8. INSTALLATION SHOWN IS FOR NATIONAL, STATE, AND LOCAL CODES
- Product Information:**
 - PANDUIT P/N
 - HB0B1L4BT08W



MODEL FILENAME		09V098DX/01.PRT	
CAD FILENAME/LAYERS		09V098DX_DC/01A.PRT	
 CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19 POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X. +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/- 1°	
DRAWN BY MAV		SCALE NONE	
DATE 2-24-11		DRAWING NO. 09V098DX	
CHK'D KRKE		DWG 	