samtec



(2,00 mm) .0787"

BTMM SERIES

LOW PROFILE SQUARE POST JUMPER



SPECIFICATIONS

For complete specifications see www.samtec.com?BTMM

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Sn over 50µ" (1,27µm) Ni
Operating Temp Range:
-55°C to +105°C
RoHS Compliant:
Yes
Lead–Free Solderable:
Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594

BTMM	–	1	NO. PINS PER ROW	–	01	–	PLATING OPTION	–	ROW OPTION	–	OTHER OPTION
			01 thru 50				–T = Matte Tin		–S = Single Row –D = Double Row		"XXX" = Polarized Position (Specify position of omitted pin) (Leave blank for no option)





Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.