


Rocker Switches

Standard Size Sealed Rockette Switches




The rocker switches offer a remarkable silicone rubber seal that protects contacts and mechanisms better than conventional seal and boot combinations. The switches resist contaminants such as sand, dust and moisture with both base to frame seal and an actuator seal. **Rated:** 15 A, 125 VAC; 10 A, 250 VAC. **Spade Terminals:** Brass. Concave rocker. Illuminated versions available.

| Stock No. | Mfr.'s Type* | Circuit | Action (Momentary) | EACH  |       |       |
|-----------|--------------|---------|--------------------|-------|-------|-------|
|           |              |         |                    | 1-24  | 25-49 | 50-99 |
| 757-5520  | 8055K23Z7V   | SPST    | On-None-Off        | 7.88  | 6.24  | 6.02  |
| 757-5521  | 8055K20Z7V   | SPDT    | On-Off-On          | 9.06  | 7.16  | 6.92  |
| 757-5525  | 8055K43Z7V   | DPST    | On-None-Off        | 10.06 | 8.12  | 7.83  |
| 757-5522  | 8055K40Z7V   | DPDT    | On-Off-On          | 11.43 | 9.04  | 8.73  |
| 757-5523  | 8055K52Z7V   | DPDT    | On-Off-(On)        | 12.91 | 10.42 | 10.06 |

\*Other terminations available.

Full Size New Generation Rockers



This all new line of rockers offers European styling, ergonomic design with the solid durability you've come to expect from Eaton switches. Rockers and bezels for the NGR series are molded in a soft matte finish. Illuminated and non-illuminated versions are available.

Non-Illuminated (Rated: 15 A @ 125 VAC, 10 A @ 250 VAC, 15 A @ 28 VDC)

| Stock No. | Mfr.'s Type   | Circuit | Action (Momentary) | EACH  |       |       |
|-----------|---------------|---------|--------------------|-------|-------|-------|
|           |               |         |                    | 1-24  | 25-49 | 50-99 |
| 757-5539  | NGR20011BN00N | DPST    | On-None-Off        | 8.14  | 6.44  | 6.21  |
| 757-5540  | NGR20031BN00N | DPDT    | On-None-Of         | 11.10 | 8.79  | 8.47  |
| 757-5541  | NGR20041BN00N | DPDT    | On-Off-On          | 9.41  | 7.45  | 7.18  |
| 757-5542  | NGR20051BN00N | DPDT    | On-Off-(On)        | 11.30 | 8.95  | 8.62  |

Illuminated (Rated: 15 A @ 125 VAC, 10 A @ 250 VAC, 15 A @ 28 VDC)

|          |               |      |               |       |       |       |
|----------|---------------|------|---------------|-------|-------|-------|
| 757-5543 | NGR25011BNA0N | DPST | On-None-Off   | 12.09 | 9.76  | 9.40  |
| 757-5544 | NGR25481BNAAN | DPDT | On-None-On    | 13.92 | 11.24 | 10.83 |
| 757-5545 | NGR25681BNAAN | DPDT | On-Off-On     | 13.92 | 11.24 | 10.83 |
| 757-5546 | NGR25881BNAAN | DPDT | (On)-Off-(On) | 14.08 | 11.36 | 10.95 |


NGR Rocker Button (Ordered Separately; Does Not Include Lens)

| Stock No. | Mfr.'s Type   | Fig. | Description           | EACH |       |       |
|-----------|---------------|------|-----------------------|------|-------|-------|
|           |               |      |                       | 1-24 | 25-49 | 50-99 |
| 757-5567  | 1B            | A    | Black Rocker, No Lens | 1.60 | 1.26  | 1.20  |
| 757-5568  | 2C00050000500 | B    | Lens Hole Top/Bottom  | 2.27 | 1.85  | 1.79  |
| 757-5569  | 2A000500      | C    | Lens Hole Top         | 1.63 | 1.28  | 1.23  |
| 757-5570  | 2B000500      | D    | Lens Hole Bottom      | 1.63 | 1.28  | 1.23  |


NGR Rocker Lens (Ordered Separately)

| Stock No. | Mfr.'s Type | Color | EACH |       |       |
|-----------|-------------|-------|------|-------|-------|
|           |             |       | 1-24 | 25-49 | 50-99 |
| 757-5551  | 28-5863     | Green | .30  | .23   | .22   |
| 757-5552  | 28-5863-3   | Amber | .30  | .23   | .22   |
| 757-5553  | 28-5863-2   | Red   | .30  | .23   | .22   |

Midsize Snap In AC Rocker Switches



Matte Finish/Rounded Bezel/Contoured Rocker — 1500/2500 Series



These switches come in lighted and non-lighted versions in a variety of standard or custom colors. They are UL, CSA and VDE approved. Ideal applications include appliances, electronic instrumentation, data processing, communications, medical and office equipment. Options available are legend stamping, solder lugs, independent lamp circuits, special and matched colors, high inrush capabilities. Aesthetically pleasing yet ruggedly functional with traditional Eaton quality, these switches are ideal for up-front applications where both appearance and reliability are required.

Non-Illuminated Type (Rated: 15 A, 125 V; 10 A, 250 V)

| Stock No. | Mfr.'s Type | Fig. | Circuit | Action (Momentary) | EACH |       |       |
|-----------|-------------|------|---------|--------------------|------|-------|-------|
|           |             |      |         |                    | 1-24 | 25-49 | 50-99 |
| 757-5013  | 1500-11E    | A    | SPST    | On-None-Off        | 1.03 | .90   | .75   |
| 757-5014  | 1501-11E    | A    | SPST    | (On)-None-Off      | 1.85 | 1.63  | 1.35  |
| 757-5015  | 1502-11E    | A    | SPDT    | On-None-On         | 1.33 | 1.17  | .98   |
| 757-5016  | 1504-11E    | A    | SPDT    | On-Off-On          | 1.83 | 1.60  | 1.33  |
| 757-5017  | 2500-11E    | B    | DPST    | On-None-Off        | 1.64 | 1.44  | 1.20  |
| 757-5018  | 2501-11E    | B    | DPST    | (On)-None-Off      | 1.93 | 1.70  | 1.43  |
| 757-5019  | 2502-11E    | B    | DPDT    | On-None-On         | 2.22 | 1.94  | 1.63  |

Illuminated Type (Rated: 15 A, 125 V; 10 A, 250 V)


| Stock No. | Mfr.'s Type* | Fig. | Circuit | Action      | Lens Color | EACH |       |       |
|-----------|--------------|------|---------|-------------|------------|------|-------|-------|
|           |              |      |         |             |            | 1-24 | 25-49 | 50-99 |
| 757-5007  | 1500R11E     | C    | SPST    | On-None-Off | Red        | 2.40 | 2.15  | 1.78  |
| 757-5008  | 1500A11E     | C    | SPST    | On-None-Off | Amber      | 2.50 | 2.24  | 1.89  |
| 757-5009  | 1500G11E     | C    | SPST    | On-None-Off | Green      | 2.50 | 2.24  | 1.89  |
| 757-5010  | 2500R11E     | D    | DPST    | On-None-Off | Red        | 2.82 | 2.36  | 1.94  |
| 757-5011  | 2500A11E     | D    | DPST    | On-None-Off | Amber      | 3.50 | 3.15  | 2.63  |
| 757-5012  | 2500G11E     | D    | DPST    | On-None-Off | Green      | 2.85 | 2.56  | 2.14  |

\*Other lamp voltages are available.

Rocker Switches with On-Off Legends (Rated: 15 A, 125 V; 10 A, 250 V)

| Stock No. | Mfr.'s Type | Fig. | Circuit | Action      | EACH |       |       |
|-----------|-------------|------|---------|-------------|------|-------|-------|
|           |             |      |         |             | 1-24 | 25-49 | 50-99 |
| 757-5020  | 1500-11E671 | A    | SPST    | On-None-Off | 1.33 | 1.17  | .98   |
| 757-5021  | 2500-11E735 | B    | DPST    | On-None-Off | 2.05 | 1.71  | 1.43  |

Gloss Finish/Flat Bezel/Two-Face Rocker — 1600/2600 Series



Non-Illuminated (Rated: 16 A, 125 VAC/250 VAC)

| Stock No. | Mfr.'s Type | Fig. | Circuit | Action (Momentary) | EACH |       |       |
|-----------|-------------|------|---------|--------------------|------|-------|-------|
|           |             |      |         |                    | 1-24 | 25-49 | 50-99 |
| 757-3012  | 1600-11E    | E    | SPST    | On-None-Off        | 1.35 | 1.17  | .97   |
| 757-3013  | 1601-11E    | E    | SPST    | (On)-None-Off      | 1.25 | 1.10  | .93   |
| 757-3014  | 1602-11E    | E    | SPDT    | On-None-On         | 1.52 | 1.33  | 1.12  |
| 757-3015  | 1604-11E    | E    | SPDT    | On-Off-On          | 1.64 | 1.44  | 1.20  |
| 757-3016  | 2600-11E    | F    | DPST    | On-None-Off        | 1.77 | 1.56  | 1.29  |
| 757-3017  | 2601-11E    | F    | DPST    | (On)-None-Off      | 2.14 | 1.89  | 1.56  |
| 757-3018  | 2602-11E    | F    | DPDT    | On-None-On         | 2.35 | 2.11  | 1.74  |
| 757-3019  | 2604-11E    | F    | DPDT    | On-Off-On          | 2.66 | 2.39  | 1.98  |

Illuminated (Rated: 16 A, 125 VAC/250 VAC)

| Stock No. | Mfr.'s Type | Fig. | Circuit | Action      | Lens Color | EACH |       |       |
|-----------|-------------|------|---------|-------------|------------|------|-------|-------|
|           |             |      |         |             |            | 1-24 | 25-49 | 50-99 |
| 757-3020  | 1600R11E    | G    | SPST    | On-None-Off | Red        | 2.51 | 2.24  | 1.89  |
| 757-3021  | 1600A11E    | G    | SPST    | On-None-Off | Amber      | 2.51 | 2.24  | 1.89  |
| 757-3024  | 1600G11E    | G    | SPST    | On-None-Off | Green      | 2.65 | 2.37  | 2.00  |
| 757-3025  | 2600R11E    | H    | DPST    | On-None-Off | Red        | 3.14 | 2.81  | 2.32  |
| 757-3026  | 2600A11E    | H    | DPST    | On-None-Off | Amber      | 3.14 | 2.81  | 2.32  |
| 757-3027  | 2600G11E    | H    | DPST    | On-None-Off | Green      | 3.14 | 2.81  | 2.32  |

High Inrush "H" Series (Rated: 22 A, 125 VAC; 16 A, 250 VAC)

| Stock No. | Mfr.'s Type | Fig. | Circuit | Action      | Description          | EACH |       |       |
|-----------|-------------|------|---------|-------------|----------------------|------|-------|-------|
|           |             |      |         |             |                      | 1-24 | 25-49 | 50-99 |
| 757-3028  | 1600H11E    | E    | SPST    | On-None-Off | Black Gloss          | 1.54 | 1.35  | 1.12  |
| 757-3029  | 1600HR11E   | F    | SPST    | On-None-Off | Red Lens, 125 V Neon | 2.70 | 2.42  | 2.03  |
| 757-3030  | 2600H11E    | G    | DPST    | On-None-Off | Black Gloss          | 2.02 | 1.78  | 1.47  |
| 757-3031  | 2600HR11E   | H    | DPST    | On-None-Off | Red Lens, 125 V Neon | 3.07 | 2.75  | 2.27  |

Check Pricing And Availability Of All Items On The Internet At [www.alliedelec.com](http://www.alliedelec.com)

ALLIED ► 217