



**Series CE/CT  
.156" Connectors**

**.156" (3.96 mm) End and  
Through Connectors  
Available in 2-24 Circuits  
with Optional Cover**



**Dimensions**




**Snap-on Covers EC**

**Snap-on Covers TC**



**Strain Relief Combination Cover SCC**



**Dimensions**

| No. of Circuits       |   | 2              | 3               | 4               | 5               | 6               | 7                | 8                | 9                | 10               | 11               | 12               | 13               | 14               | 15               | 16               | 17               | 18               | 19               | 20               | 21               | 22               | 23               | 24               |
|-----------------------|---|----------------|-----------------|-----------------|-----------------|-----------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|
| Dim. in<br>in. / (mm) | a | .312<br>(7.92) | .468<br>(11.89) | .624<br>(15.85) | .780<br>(19.81) | .936<br>(23.77) | 1.092<br>(27.74) | 1.248<br>(31.70) | 1.404<br>(35.66) | 1.560<br>(39.62) | 1.716<br>(43.59) | 1.872<br>(47.55) | 2.028<br>(51.51) | 2.184<br>(55.47) | 2.340<br>(59.44) | 2.496<br>(63.40) | 2.652<br>(67.36) | 2.808<br>(71.32) | 2.964<br>(75.29) | 3.120<br>(79.25) | 3.276<br>(83.21) | 3.432<br>(87.17) | 3.588<br>(91.14) |                  |
|                       | b | .156<br>(3.96) | .312<br>(7.92)  | .468<br>(11.89) | .624<br>(15.85) | .780<br>(19.81) | .936<br>(23.77)  | 1.092<br>(27.74) | 1.248<br>(31.70) | 1.404<br>(35.66) | 1.560<br>(39.62) | 1.716<br>(43.59) | 1.872<br>(47.55) | 2.028<br>(51.51) | 2.184<br>(55.47) | 2.340<br>(59.44) | 2.496<br>(63.40) | 2.652<br>(67.36) | 2.808<br>(71.32) | 2.964<br>(75.29) | 3.120<br>(79.25) | 3.276<br>(83.21) | 3.432<br>(87.17) | 3.588<br>(91.14) |

**Part Number**

| No. of Circuits 2-24 (Contact Factory For Circuit Availability) |              |              |              |              | □□ = Number of Circuits |
|-----------------------------------------------------------------|--------------|--------------|--------------|--------------|-------------------------|
| Version                                                         | Wire Size    |              |              |              | Dimensions              |
|                                                                 | AWG 24       | AWG 22       | AWG 20       | AWG 18       | c inches (mm)           |
| End Connector                                                   | CE156F24- □□ | CE156F22- □□ | CE156F20- □□ | CE156F18- □□ | .33 (8.4)               |
| Through Connector                                               | CT156F24- □□ | CT156F22- □□ | CT156F20- □□ | CT156F18- □□ | .35 (9.0)               |
| AWG Identification Color                                        | Black        | Red          | Brown        | Orange       |                         |

|                                      |             |
|--------------------------------------|-------------|
| Snap-on Cover for End connectors     | EC 156F- □□ |
| Snap-on Cover for Through connectors | TC 156F- □□ |
| Strain Relief Combination Cover      | SCC156F- □□ |