


**Part Number: 90500-4109**

2.54mm Vertical, ZIF Receptacle, 9 Circuits, Kinked Tails

*Series Image - Reference only*

Status:	OBsolete
Replacement:	Contact Molex
Series:	90500
Category:	FFC/FPC Connectors

Product Environmental ComplianceEU RoHS: Compliance Status Not ReviewedChina RoHS:REACH SVHC: Not ReviewedLow-Halogen Status: Not Reviewed**Part Detail****General**

Status	Obsolete
Category	FFC/FPC Connectors
Series	90500
Product Name	N/A

Physical

Circuits (Loaded)	9
Circuits (maximum)	9
Contact Position	N/A
Durability (mating cycles max)	50
Entry Angle	Vertical
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Wire/Cable Type	FFC only

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V DC

Material Info**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)