

Designer's Kit



Kit Contents for C391:

- MSS1038 Power Inductors
- 31 values, 3 of each

Part Number Table

Inductance	Current Rating	Part Number
1 μ H	12.1A	MSS1038-102NLB
1.5 μ H	11.06A	MSS1038-152NLB
2.5 μ H	9.26A	MSS1038-252NLB
3.8 μ H	7.64A	MSS1038-382NLB
5.2 μ H	6.14A	MSS1038-522NLB
7 μ H	5.6A	MSS1038-702NLB
10 μ H	4.52A	MSS1038-103NLB
12 μ H	4.04A	MSS1038-123NLB
15 μ H	3.86A	MSS1038-153NLB
18 μ H	3.52A	MSS1038-183NLB
22 μ H	3.3A	MSS1038-223NLB
27 μ H	2.84A	MSS1038-273NLB
33 μ H	2.62A	MSS1038-333NLB
39 μ H	2.34A	MSS1038-393NLB
47 μ H	2.22A	MSS1038-473NLB
56 μ H	2.04A	MSS1038-563NLB

Inductance	Current Rating	Part Number
68 μ H	1.82A	MSS1038-683NLB
82 μ H	1.6A	MSS1038-823NLB
100 μ H	1.46A	MSS1038-104NLB
120 μ H	1.34A	MSS1038-124NLB
150 μ H	1.22A	MSS1038-154NLB
180 μ H	1.16A	MSS1038-184NLB
220 μ H	0.99A	MSS1038-224NLB
270 μ H	0.91A	MSS1038-274NLB
330 μ H	0.82A	MSS1038-334NLB
390 μ H	0.74A	MSS1038-394NLB
470 μ H	0.7A	MSS1038-474NLB
560 μ H	0.56A	MSS1038-564NLB
680 μ H	0.52A	MSS1038-684NLB
820 μ H	0.49A	MSS1038-824NLB
1000 μ H	0.46A	MSS1038-105NLB