



SANDVIK BELZER

For slotted head screws

Finish: blade fine polished and bright chrome plated, entirely hardened, tip black oxidized. Unloosable colour code on both ends of handle as time-saving aid for identification of the respective screw.


Material: blade of VANADIUM-EXTRA.

Ergonomically developed 3-component handle of polypropylene and thermoplastic elastomere.

ergo®



DIN 5265 ISO 2380-2
Tip DIN 5264-A, ISO 2380-1.



Product code	EAN code 731415+		mm	mm	mm	mm	mm	mm	
BE-8010	0010615	5	0,4	2,5	50	16x102	152	17	
BE-8210	1838584	5	0,4	2,5	75	16x102	177	18	
BE-8020	0010639	5	0,5	3	50	16x102	152	20	
BE-8020L	1838591	5	0,5	3	75	16x102	177	22	
BE-8220	0047741	5	0,5	3	125 *	16x102	227	22	
BE-8030	0010653	5	0,6	3,5	75	20x122	197	35	
BE-8230	0047758	5	0,6	3,5	125	20x122	247	38	
BE-8040	0010677	5	0,8	4	100	20x122	222	38	
BE-8240	0047765	5	0,8	4	175 *	20x122	297	47	
BE-8150	0010707	5	1	5,5	100	27x122	222	70	
BE-8250	0047772	5	1	5,5	150	27x122	272	75	
BE-8250L	1838607	5	1	5,5	200	27x122	322	90	
BE-8155	0010721	5	1,2	6,5	125	36x122	247	101	
BE-8255	0047789	5	1,2	6,5	150	36x122	272	114	



With hexagon collar



Product code	EAN code 731415+		mm	mm	mm	mm	mm	mm	
BE-8160	0010745	5	1,2	8	125	36x122	247	11	142
BE-8260	0047796	5	1,2	8	175	36x122	297	11	165
BE-8865	0010851	5	1,6	8	175	36x161	336	13	176
BE-8870	0010875	5	1,6	10	175	36x161	336	13	200
BE-8880	0010899	5	2	12	200	36x161	361	13	272
BE-8890	0010905	5	2,5	14	200	36x161	361	16	276

Stubby type



For work in confined spaces.



BE-8330	1838614	5	0,6	3,5	25	36x58	83	43	
BE-8340	1838621	5	0,8	4	25	36x58	83	43	
BE-8350	1838638	5	1	5,5	25	36x58	83	43	
BE-8450	1838645	5	1	5,5	45	36x58	103	51	
BE-8355	1838652	5	1,2	6,5	25	36x58	83	43	
BE-8455	1838669	5	1,2	6,5	45	36x58	103	25	
BE-8360	1838676	5	1,2	8	25	36x58	83	50	