

## BBP®31 and BBP®33 General Identification Materials:

### B-7569 Pre-Printed GHS / CLP Chemical Labels

- Blank labels with pre-printed red diamonds allow printer to produce 2-color GHS / CLP labels in one print pass
- 3 sizes of labels, each with 6 diamond layouts that match templates in MarkWare™ Software
- Indoor/outdoor vinyl material withstands exposure to moisture, chemicals and handling
- MarkWare Software v3.9.1 or higher required (upgrades available for current MarkWare owners)

Service temp: -4°F to 180°F Application temp: 50°F to 180°F  
Average Outdoor Durability: 3-5 years



| Fits Printer Model(s) | Catalog #          | B#     | Material | Legend | Label Height Inch (mm) | Label Width Inch (mm) | Labels Per Row | Labels Per Roll | Rec. Ribbon |
|-----------------------|--------------------|--------|----------|--------|------------------------|-----------------------|----------------|-----------------|-------------|
| BBP31, BBP33          | B30-260-7569-CLP1  | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP1  | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP1  | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |
| BBP31, BBP33          | B30-260-7569-CLP2  | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP2  | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP2  | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |
| BBP31, BBP33          | B30-260-7569-CLP3A | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP3A | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP3A | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |
| BBP31, BBP33          | B30-260-7569-CLP3B | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP3B | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP3B | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |
| BBP31, BBP33          | B30-260-7569-CLP4A | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP4A | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP4A | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |
| BBP31, BBP33          | B30-260-7569-CLP4B | B-7569 | Vinyl    |        | 2.170 (55.0)           | 3.350 (85.0)          | 1              | 340             | B30-R10000  |
| BBP31, BBP33          | B30-261-7569-CLP4B | B-7569 | Vinyl    |        | 2.950 (75.0)           | 4.330 (110.0)         | 1              | 270             | B30-R10000  |
| BBP31, BBP33          | B30-262-7569-CLP4B | B-7569 | Vinyl    |        | 4.130 (105.0)          | 6.100 (155.0)         | 1              | 200             | B30-R10000  |




## MarkWare™ Software now includes a GHS / CLP Label Module

- 18 pre-formatted label layouts and approved GHS symbols are built-in
- User selects approved pre-worded hazard statements and GHS symbols which then automatically populates into layout – no need to type everything in
- Prompts for additional variable data which then auto-populates into layout
- Indoor/outdoor vinyl material withstands exposure to moisture, chemicals and handling
- Choose a second language and MarkWare auto-populates in the second language

| Catalog # | Description        |
|-----------|--------------------|
| 20700     | MarkWare™ Software |

Already own MarkWare Software?

Go to [www.BradyID.com/markware](http://www.BradyID.com/markware) to upgrade your current MarkWare to v3.9.1 for the GHS / CLP Label Module.



View all BBP®33 and BBP®33 Print Ribbon parts on page 329.