


**Part Number: 70565-0015**

2.54mm Pitch SL™ Header, Single Row, Vertical, 4.57mm Pocket, Shrouded, with Press-fit Plastic Peg, 16 Circuits, Tin (Sn) Plating



Series Image - Reference only

Status: **OBsolete**
Replacement: [70563](#) (no peg)
Series: 70565
Category: PCB Headers

Mates With Part(s):
[70004](#)**Product Environmental Compliance****EU RoHS:** Compliance Status Not Reviewed**China RoHS:****REACH SVHC:** Not Reviewed**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	PCB Headers
Series	70565
Application	Signal, Wire-to-Board
Obsolete Date	2004/09/01
Product Name	SL™

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	3A
Voltage - Maximum	250V

Material Info

UPC	800754664578
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be](#)

[available for this part](#)