



Ring Tongues – Non-Insulated Butted Seam 16-14 AWG




Product Number†	UPC (054007-)	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.	Terminals per Case
MU14-4R/SK	01364	16-14	4	0.25	0.22	0.60	0.47	0.030	0.25	0.090	1000
MU14-6R/SK	01366	16-14	6	0.25	0.22	0.60	0.47	0.030	0.25	0.090	1000
MU14-8R/LK	01371	16-14	8	0.31	0.33	0.74	0.58	0.030	0.25	0.090	1000
MU14-10RK	01372	16-14	10	0.33	0.29	0.70	0.54	0.030	0.25	0.090	1000
MU14-10R/LK	01373	16-14	10	0.31	0.33	0.74	0.58	0.030	0.25	0.090	1000
MU14-14R/SK	01374	16-14	1/4	0.47	0.40	0.89	0.65	0.030	0.25	0.090	1000




MU14-4R/S
Stud Size 4
Wire Range 16-14




MU14-6R/S
Stud Size 6
Wire Range 16-14




MU14-8R/L
Stud Size 8
Wire Range 16-14



MU14-10R
Stud Size 10
Wire Range 16-14



MU14-10R/L
Stud Size 10
Wire Range 16-14



MU14-14R/S
Stud Size 1/4
Wire Range 16-14