


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0366970052
Status: Active - Custom
Overview: handylink
Description: HandyLink®-to-USB "B" Cable Assembly, Straight Overmold, 2.0m (6.56') Cable Length



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-36697-001 \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	36697
Comments	Please reference Application Specification AS-44828-001 when designing
Connector to Connector	HandyLink®-to-USB Type B
Overview	handylink
Product Name	HandyLink®, USB
Physical	
Cable Length	2.0m (6.56')
Circuits (Loaded)	16, 4
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold, Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Pitch - Mating Interface	0.80mm (.031")
Plating min - Mating	0.102µm (4µ"), 1.270µm (50µ")
Plating min - Termination	1.270µm (50µ"), 5.080µm (200µ")
Single Ended	No
Termination Interface: Style	Solder or Weld
Waterproof / Dustproof	No
Wire Insulation Diameter	0.70-1.15mm (.026-.045")
Wire Size AWG	26, 28
Wire/Cable Type	PVC

Electrical	
Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers	
Product Specification	PS-36697-001
Sales Drawing	SD-36697-006

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
36697Series

Mates With
44828 HandyLink® Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION