

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		H2	REVISED PER ECO-07-008008	10APR07	JDP	CWR

D

C

B



A

D


C

B

A



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 2.54μm [.000100] MIN TIN-LEAD OVER 1.27μm [.000050] MIN NICKEL.
- 3 TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 4 ACCEPTS #2 SELF-TAPPING SCREW, .250 LONG REF.
- 5. MATES WITH 6 POSITION SHIELDED DIN PLUG 212437-4.
- 6 BRASS PER ASTM B36.
- 7 2.54μm [.000100] MIN TIN OVER 1.27μm [.000050] MIN NICKEL.



OBSOLETE	7	9-211509-0
	2	211509-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN A.STAUB BG CHK —	8/12/91 —	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME	RECEPTACLE ASSY, RIGHT ANGLE, 6 POSITION, CIRCULAR DIN —							
		0 PLC ± —		PRODUCT SPEC									
		1 PLC ± —		108-10047									
		2 PLC ± 0.13[.005]		APPLICATION SPEC									
		3 PLC ± —		114-40025									
4 PLC ± —		ANGLES ± —		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL		FINISH		—		A2	00779	C-211509		—			
		SEE TABLE		CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 1	REV	H2