


7905 Series

D-SUB Straight Type



Material:

Housing: 30% Glass Filled PBT UL94V-0.

Contacts: Brass.

Shell: Steel

Electrical Characteristics:

Current Rating: 1 A.

Dielectric Withstanding Voltage: AC 1000V.






Insulator Resistance: 1000M Ω min.

Contact Resistance: 20m Ω max.

Operating Temperature: -55°C~+105°C.

Features:

* Mates with: 7901, 7907, 7908.



Position	Dimension				
	A	B	C	D	E
9	16.92	24.99	30.81	19.28	16.33
15	25.25	33.32	39.14	27.51	24.66
25	38.96	47.04	53.04	41.30	38.38
37	55.42	63.50	69.32	57.71	54.84

Ordering information

7905-

Series

37

Position

M

M: Male
F: Female

T

T: Tin Shell
E: Zinc Shell

U

U: Blue
B: Black
W: White

C

C: Selective Gold
Plated
G: Gold Plated

00

00: G/F

N1

Blank: Standard Type
N1: See Page A173

A

A: Tray
Package