

## ROTARY SWITCHES



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6




Fig. 7

| Retail Part No. | Bulk Part No. | Fig. No. | Poles/Throws | Amps 125 VAC | Amps 250 VAC | Action       | Actuator      | Terminal Type | Mounting Style   | Mounting Hole (In) | Hardware | Spec Drawing Page No. |
|-----------------|---------------|----------|--------------|--------------|--------------|--------------|---------------|---------------|------------------|--------------------|----------|-----------------------|
| 35-859          | 35-859-BU     | 1        | SPST         | 3            | 1.5          | On/Off       | White Plastic | 6" Wire Leads | Snap-In          | 0.500              |          | 301-A                 |
| 35-855          | 35-855-BU     | 2        | SPST         | 6            | 3            | On/Off       | Brass Knob    | 6" Wire Leads | Threaded Bushing | 0.375              | KN, FN   | 301-B                 |
| 35-856          | 35-856-BU     | 3        | SPST         | 6            | 3            | On/Off       | Black Plastic | 6" Wire Leads | Threaded Bushing | 0.375              | N, FN    | 301-C                 |
| 35-1857         | 35-1857-BU    | 4        | SP3T         | 6            | 3            | Off/On/On/On | Brass Knob    | 6" Wire Leads | Threaded Bushing | 0.375              | N, FN    | 301-D                 |

| Retail Part No. | Bulk Part No. | Fig. No. | Amps (Cont.) | Amps 125 VAC | Amps 125 VDC | Positions  | Poles | Index | Actuator     | Terminal Type | Mounting Style | Mounting Hole (In) | Hardware   | Spec Drawing Page No. |
|-----------------|---------------|----------|--------------|--------------|--------------|------------|-------|-------|--------------|---------------|----------------|--------------------|------------|-----------------------|
| 35-375          | 35-375-BU     | 5        |              | 0.3+         |              | 6          | 2     | 30°   | 1/4" Metal   | Sd Eyelet     | Shorting       | 0.375              | N, LR      | 301-E                 |
| 35-376          | 35-376-BU     | 5        |              | 0.3+         |              | 12         | 1     | 30°   | 1/4" Metal   | Sd Eyelet     | Shorting       | 0.375              | N, LR      | 301-E                 |
| 35-377          | 35-377-BU     | 5        |              |              |              | 5          | 2     | 30°   | 1/4" Metal   | Sd Eyelet     | Non-Shorting   | 0.375              | N, LR      | 301-E                 |
| 35-378          | 35-378-BU     | 5        |              | 0.3+         |              | 3          | 3     | 30°   | 1/4" Metal   | Sd Eyelet     | Non-Shorting   | 0.375              | N, LR      | 301-E                 |
| 35-379          | 35-379-BU     | 5        |              | 0.3+         |              | 4          | 3     | 30°   | 1/4" Metal   | Sd Eyelet     | Shorting       | 0.375              | N, LR      | 301-E                 |
| 35-1212         |               | 6        | 6            | 250mA*       |              | 12 No Stop | 1     | 30°   | 1/2" Metal   | Sd Eyelet     | Non-Shorting   | 0.250              | N, LR, W   | 301-F                 |
| 35-1226         |               | 6        | 6            | 250mA*       |              | 6 No Stop  | 2     | 30°   | 1/2" Metal   | Sd Eyelet     | Non-Shorting   | 0.250              | N, LR, W   | 301-F                 |
| 35-1306         |               | 7        | 5            | 2.5          | 350mA        | 6          | 1     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR      | 301-G                 |
| 35-1312         |               | 7        | 5            | 2.5          | 350mA        | 12 No Stop | 1     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR      | 301-G                 |
| 35-1314         |               | 7        | 5            | 2.5          | 350mA        | 12         | 1     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR, StR | 301-G                 |
| 35-1324         |               | 7        | 5            | 2.5          | 350mA        | 4          | 2     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR      | 301-G                 |
| 35-1334         |               | 7        | 5            | 2.5          | 350mA        | 4          | 3     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR      | 301-G                 |
| 35-1343         |               | 7        | 5            | 2.5          | 350mA        | 3          | 4     | 30°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR      | 301-G                 |
| 35-1323         |               | 7        | 5            | 2.5          | 350mA        | 8          | 1     | 45°   | 1/4" Plastic | Sd Lug        | Non-Shorting   | 0.386              | N, LR, StR | 301-G                 |

Notes: \*Or 28VDC  
Adj.=Adjustable Stop  
+Or 30V DC  
Non-Shorting=break before make

FN=Face Nut  
KN=Knurled Nut  
LR=Locking Ring  
N=Nut

Sd=Solder  
StR=Stop Ring  
W=Washer

## SLIDE SWITCHES



Fig. 8



Fig. 9




Fig. 10




Fig. 11



Fig. 12

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Funct. | Poles & Throws | Amps 125 VAC | Amps 250 VAC | Amps 30 VAC | Amps 125 VDC | Actuator Style | Terminal Type             | Mounting Style | Spec Drawing Page No. |
|-----------------|---------------|----------|----------------|----------------|--------------|--------------|-------------|--------------|----------------|---------------------------|----------------|-----------------------|
| 35-202          | 35-202-BU     | 8        | On/On          | SPDT           |              |              | 0.30        | 1/2          | Black Plastic  | Solder Lug                | Surface        | 301-H                 |
| 35-204          | 35-204-BU     | 9        | On/On          | DPDT           |              |              | 3           | 1/2          | Black Plastic  | Solder Lug                | Surface        | 301-I                 |
| 35-210          | 35-210-BU     | 10       | On/On          | SPDT           | 6            |              |             |              | Black Plastic  | Printed Circuit Board Lug | Surface        | 301-J                 |
| 35-222          | 35-222-BU     | 11       | On/On          | DPDT           | 6            | 3            |             |              | Black Plastic  | Printed Circuit Board Lug | Surface        | 301-K                 |
| 35-242          | 35-242-BU     | 12       | On/On          | DPDT           | 11           |              |             |              | Black Plastic  | Solder Lug                | Surface        | 301-L                 |

| Retail Part No. | Bulk Part No. | Fig. No. | Number of Positions | Profile       | Spec Drawing Page No. |
|-----------------|---------------|----------|---------------------|---------------|-----------------------|
| 35-953          |               | 13       | 4                   | Side Actuated | 301-M                 |
| 35-957          |               | 13       | 8                   | Side Actuated | 301-M                 |
| 35-961          | 35-961-BU     | 14       | 1                   | Standard      | 301-N                 |
| 35-962          |               | 14       | 2                   | Standard      | 301-N                 |
| 35-963          |               | 14       | 3                   | Standard      | 301-N                 |
| 35-964          | 35-964-BU     | 14       | 4                   | Standard      | 301-N                 |
| 35-965          |               | 14       | 5                   | Standard      | 301-N                 |
| 35-966          | 35-966-BU     | 14       | 6                   | Standard      | 301-N                 |
| 35-967          |               | 14       | 7                   | Standard      | 301-N                 |
| 35-968          | 35-968-BU     | 14       | 8                   | Standard      | 301-N                 |
| 35-969          |               | 14       | 9                   | Standard      | 301-N                 |
| 35-970          | 35-970-BU     | 14       | 10                  | Standard      | 301-N                 |
| 35-974          |               | 14       | 12                  | Standard      | 301-N                 |
| 35-971          |               | 15       | 8                   | Right Angle   | 301-N                 |



Fig. 13



Fig. 14



Fig. 15

Rating:  
100mA@50Vdc (carry)  
100mA@5Vdc  
25mA@25Vdc

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

## ROTARY, SLIDE & DIP SWITCHES (Cont.)

