

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

U

-

P

LTR

DESCRIPTION

DATE

DGN

APVD


P

REVISED PER ECO-11-005139

28MAR11

RK




HMR



FOR CONTINUOUS

5.8
4.6

FOR SINGLES

5.3
4.0

NOTES:

1. WIRE RANGE

CONDUCTOR: 0.7mm² - 2.1mm²

INSULATION DIA: 2.3mm - 3.1mm

2. FOR CRIMPING DETAILS REFER

UTILUX CRIMP CHART No. H1972

LOOSE PIECE	NICKEL SILVER	RECEPTACLE, H1972B/150	1-1627057-9
LOOSE PIECE	BRASS	RECEPTACLE, H1972/10000	1-1627057-7
REEL FORM	NICKEL SILVER	RECEPTACLE, H1972B/R8000	1-1627057-5
REEL FORM	BRASS PRE-TIN	RECEPTACLE, H1972ET/R8000	1-1627057-6
REEL FORM	BRASS	RECEPTACLE, H1972/R8000	1-1627057-4
LOOSE PIECE	BRASS	RECEPTACLE, H1972/150	1-1627057-1
REMARKS	MATERIAL	DESCRIPTION	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

W.RIEDE 28.10.04

CHK

H.THAH 28.10.04

APVD

W.RIEDE 28.10.04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

ALL DIMENSIONS IN mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DIMENSION (mm) TOLERANCE (mm)

LESS THAN 10 0.4


OVER 10 TO 30 0.5

OVER 30 TO 80 0.7

OVER 80 TO 250 1.0


ANGLES ±2°

MATERIAL



FINISH

-

UNREELING DIRECTION
FROM TOP OF REEL

TE Connectivity

RECEPTACLE, QC 6.3

SIZE
A3

CAGE CODE

DRAWING NO

C-1627057

RESTRICTED TO

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV P