








CONNECTOR SPECIFICATION:

VOLTAGE RATING	250VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67 WHEN MATED
OPERATING TEMPERATURE	FLEXING: -5°C TO +80°C STATIC: -30°C TO +80°C

ITEM	COMPONENT	MATERIAL	FINISH
7	LABEL	VINYL	BLACK/YELLOW
6	O-RING	VITON	RED
5	COUPLER	NICKEL-BRASS	TEFLON COATED
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	PUR	BLACK
2	OVERMOLD	TPE	YELLOW
1	CABLE #18-4 (COPPER STRANDING) 4 CONDUCT. 300V	JACKET: TPE	YELLOW

1200680194	884A30K03M040	13.12' +6.50" -0 [4.0M +165.1 -0]
1200680193	884A30K03M030	9.84' +3.50" -0 [3.0M +88.9 -0]
1200680192	884A30K03M020	6.56' +3.50" -0 [2.0M +88.9 -0]
1200680191	884A30K03M015	4.92' +2.19" -0 [1.5M +55.6 -0]
1200680190	884A30K03M010	3.28' +2.19" -0 [1.0M +55.6 -0]
1200680189	884A30K03M006	1.97' +1.75" -0 [0.6M +44.5 -0]
1200680188	884A30K03M005	1.64' +1.75" -0 [0.5M +44.5 -0]
1200680187	884A30K03M003	0.98' +0.75" -0 [0.3M +19.1 -0]
MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH

LABEL & COUPLING NUT EC NO: IPG2012-1061 DRWN: VOU CH'KD: KJOZWK APPR: JFMURPHY 2010/02/15		5/16/12 ! 2010/02/15	QUALITY SYMBOLS =0 =0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 				
						mm	INCH	DRAWN BY DATE		TITLE MIC IN-LINE SPLITTER ST ----- -----					
					4 PLACES	±---	±---	BBRAUCH	2010/02/04						
					3 PLACES	±---	±.005	CHECKED BY DATE							
					2 PLACES	±.13	±.010	NS	2010/02/05						
					1 PLACE	±.25	±.020	APPROVED BY DATE	 MOLEX INCORPORATED						
ANGULAR ±---°			NSTAUDIG	2010/02/15											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					MATERIAL NO.		DOCUMENT NO.				SHEET NO.				
					SEE TABLE		SD-120068-022				1 OF 1				
2					REV	SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								