



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0,4
X.XX=±0,25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. OPERATING FORCE: 425±100 CM/STANDARD
7. OPERATING TEMP: -30° to 85°C
8. CIRCUIT SP: 3 POSITIONS, 30° INDEX
9. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
10. DESIGNATE MAJOR DIMENSIONS
11. SUPPLIED HARDWARE: LOCK NUT AND WASHER NOT SHOWN.




CONTACT CONFIGURATION

Timing: Non-Shorting (BBM)



TERMINATION DETAIL

SCALE 2X



E-SWITCH®				
TITLE				
KC-13-A (10.0mm)-01-N-L-S				
SCALE	DATE	DR	DWG	REV
1.5:1	11/22/02	CJB	G510712	A

B			
A	12356	RELEASED FOR PRODUCTION	11/22/02 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			