



[Support](#) ▶ [Riser Card List](#)

Reset All

Search

If you have questions please contact [Technical Support](#), [Riser Card naming convention](#) (*) Device support limited; hardware monitoring of device may not be supported.
Note: Riser cards for SuperBlade and MicroBlade are sold with complete systems only.

Model	Category Any	Form Factor Any	Slot Position Any	Design Type Any	Output Type Any	Gen2 Any Gen3 Any	GPU_PHI Support (*) Any	NVMe (or #Ports) Any	M.2 (or #Ports) Any	Thermal Sensor Any	Auto Detect Any	Systems
RSC-88-F1  Used together with RSC-88-F2 only	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-F618H6-FTL+ SYS-F618H6-FTPTL+ SYS-F618H6-FT+ SYS-F618H6-FTPT+
RSC-88-F2  Used together with RSC-88-F1 only	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-F618H6-FTL SYS-F618H6-FTPTL+ SYS-F618H6-FTPT+ SYS-F618H6-FT+
RSC-B-A6 	Super Blade	1U	LHS	Active	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-BLG-E16 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SBI-7126TG SBI-7127RG
RSC-BLG-E16LP 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	No	No	No	No	No	SBI-7126TG
RSC-BLG-E16R 	Super Blade	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SBI-7126TG SBI-7127RG
RSC-F2F-6 	FatTwin	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-F628G2-FC0+ SYS-F628G2-FC0PT- SYS-F628G2-FT+ SYS-F628G2-FTPT+ SYS-F628G3-FC0+ SYS-F628G3-FC0PT- SYS-F628G3-FT+ SYS-F628G3-FTPT+
RSC-G-6 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-G2F-A66 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	2028GR-TR 2028GR-TRH 2028GR-TRHT 2028GR-TRT
RSC-G2FR-A66 	GPU	2U	RHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	2028GR-TR 2028GR-TRH 2028GR-TRHT 2028GR-TRT
RSC-GR-6 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: gen3:	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-GR-A88 	GPU	1U	RHS	Active	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-MLP-E8R 	MLP	1U	RHS	Passive	Output: (1) Micro LP Signal: () Micro LP	gen2: Yes gen3: Yes	No	No	No	No	No	AOM-CGP-I2M AOM-CIBF-M1M AOM-CTG-I1SM
												SYS-5028TK-HTR SYS-2028TP-HC0R-SIOM SYS-2028TP-HC1R-SIOM SYS-2028TP-HTR-SIOM SYS-6028TP-HC0R-SIOM SYS-6028TP-HC1R-SIOM SYS-6028TP-HTR-SIOM

RSC-P-6 	TwinPro	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-6028BT-HNCOR+ SYS-2028BT-HNCOR+ SYS-2028BT-HNC1R+ SYS-2028BT-HNR+ SYS-2028BT-HTR+ SYS-6028BT-HNCOR+ SYS-1029TP-DCOR SYS-1029TP-DC1R SYS-1029TP-DTR SYS-2029TP-HCOR SYS-2029TP-HC1R SYS-2029TP-HTR SYS-6029TP-HCOR SYS-6029TP-HC1R SYS-6029TP-HTR SYS-2029BT-HNCOR SYS-2029BT-HNC1R SYS-2029BT-HNR SYS-2029BT-HNTR SYS-2029BT-HTR SYS-6029BT-HNCOR SYS-2028BT-HNTR+
RSC-R1U-33 	Standard	1U	LHS	Passive	Output: (1) PCI Signal: (1) PCI-32 (33 MHz)	gen2: No gen3: No	No	No	No	No	No	5017A-EF
RSC-R1U-E16R 	Twin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	1022GG-TF 1122GG-TF 2022TC-HTRF4 2022TG-H6RF AS -2022TG-HIBQRF AS -2022TG-HLIBQRF AS -2022TG-HTRF 2122TC-H6RF4 2122TG-H6IBQRF AS -2122TG-HTRF AS -2022TC-BTRF AS -1021TM-INF+B 1021TM-T+B SYS-1017GR-TF SYS-1026GT-TF SYS-1027TR-TFF SYS-1027TR-TQF 2016TI-HTRF SYS-2027TR-H70FRF SYS-2027TR-H70QRF SYS-2027TR-H70RF SYS-2027TR-H71FRF SYS-2027TR-H71QRF SYS-2027TR-H71RF SYS-2027TR-H72FRF SYS-2027TR-H72QRF SYS-2027TR-H72RF SYS-2027TR-HTFRF SYS-2027TR-HTQRF SYS-2027TR-HTRF SYS-5017GR-TF 6016GT-TF SYS-6016TT-IBQF SYS-6016TT-IBXF SYS-6016TT-TF SYS-6017TR-TF SYS-6017TR-TFF SYS-6017TR-TQF SYS-6027TR-H70FRF SYS-6027TR-H70QRF SYS-6027TR-H70RF SYS-6027TR-H71FRF SYS-6027TR-H71QRF SYS-6027TR-H71RF SYS-6027TR-HTFRF SYS-6027TR-HTQRF SYS-6027TR-HTRF 1022TC-TF 2021TM-BIBXRF 2021TM-BTRF 1025TC-10GB 1025TC-3FB 1025TC-TB 1026TT-IBQF 1026TT-IBXF 1026TT-INFF 1026TT-TF 2026TT-H6IBQRF 2026TT-H6IBXRF 2026TT-H6RF 2026TT-HIBQRF 2026TT-HIBXRF 2026TT-HTRF 5015TB-10GB 5015TB-TB 5016TI-TF 5026TI-BTRF 5026TI-HTRF 6015TC-10GB 6015TC-LFTB 6015TC-TB 6015TW-INF 6015TW-T 6016TT-INFF 6026TT-BIBQF 6026TT-BIBQRF 6026TT-BIBXF 6026TT-BIBXRF 6026TT-BINFF 6026TT-BINFRF 6026TT-BTF 6026TT-BTRF 6026TT-H6IBQRF 6026TT-H6IBXRF 6026TT-H6RF 6026TT-HIBQF 6026TT-HIBQRF 6026TT-HIBXF 6026TT-HIBXRF 6026TT-HTF 6026TT-HTRF 6026TT-IBQF 6026TT-IBXF 6026TT-TF
RSC-R1U-E8R 	Twin	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	6015T-T 6015T-INF


RSC-R1U-UL 	Standard	1U	LHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R1U-UT 	Twin	1U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: No gen3: No	No	No	No	No	No	
RSC-R1UEP-UE 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x4 (1) UIO (PCI-E x8)	gen2: No gen3: No	No	No	No	No	No	6015X-3V 6015X-3B
RSC-R1UF-E16R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-F617R2-R72+ SYS-F617R2-RT+ SYS-F618R2-R72+ SYS-F618R2-R72PT+ SYS-F618R2-RC0+ SYS-F618R2-RC0PT+ SYS-F618R2-RC1+ SYS-F618R2-RC1PT+ SYS-F618R2-RT+ SYS-F618R2-RTN+ SYS-F618R2-RTPT+ SYS-F618R2-RTPTN+
RSC-R1UFF-E16 	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	F617H6-FT+ F617H6-FTPT+ F617R2-F72+ SYS-F617R2-F73 SYS-F617R2-FT SYS-F617R2-FT+ SYS-F617R2-FTPT+ F617R3-FT SYS-F617R3-FT+ SYS-F617R3-FTPT+ F618R2-FC0 SYS-F618R2-FT F618R3-FTL F627R2-F73 F628R2-FC0
RSC-R1UFF-E16R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-F627R3-FT SYS-F627R3-F73 F628R3-FC0 F628R3-FT
RSC-R1UFF-E8 	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	F617H6-FTL+ F617H6-FTPTL+ SYS-F618R2-FT+ SYS-F618R2-FTPT+ SYS-F618R3-FT+ SYS-F618R3-FTPT+
RSC-R1UFF-E8R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	5017R-IHDP SSG-5018A-AR12L SYS-6017R-73HDP+ SYS-6017R-73THDP+ MNL-F517H6-FT F617H6-FT+ F617H6-FTL+ F617H6-FTPT+ F617H6-FTPTL+ F617R2-F72+ SYS-F617R2-FT+ SYS-F617R2-FTPT+ SYS-F618R3-FT+ SYS-F618R3-FTPT+
RSC-R1UG-2E8AR+II 	GPU	1U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	
RSC-R1UG-2E8G 	GPU	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	SYS-6016XT-TF
RSC-R1UG-2E8G-UP 	GPU	1U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-2E8GR-UP 	GPU	1U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-A2E16-X9 	GPU	1U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TRF+ SYS-1027GR-TRFT+
RSC-R1UG-E16 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-1026GT-TF 6016GT-TF
RSC-R1UG-E16-UP 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1017GR-TF SYS-5017GR-TF SYS-1018GR-T SYS-5018GR-T

RSC-R1UG-E16-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-1027GR-TRF+ SYS-1027GR-TRFT+ SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16A 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1026GT-TRF 1026GT-TRF-FM307 1026GT-TSF
RSC-R1UG-E16A+II 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-72R2 SYS-1027GR-72RT2 SYS-1027GR-TR2 SYS-1027GR-TRT2
RSC-R1UG-E16A-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-1027GR-TQF 1027GR-TQF-FM409 1027GR-TQF-FM475 SYS-1027GR-TQFT SYS-1027GR-TRF 1027GR-TRF-FM309 1027GR-TRF-FM375 SYS-1027GR-TRFT SYS-1027GR-TSF
RSC-R1UG-E16AR+II 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TR2 SYS-1027GR-TRT2 SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16AR-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	1026GT-TRF SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF SYS-1027GR-TRFT SYS-1027GR-TRFT+ SYS-1027GR-TSF 1026GT-TRF
RSC-R1UG-E16B 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1026GT-TRF 1026GT-TSF
RSC-R1UG-E16B-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF 1027GR-TRF-FM309 SYS-1027GR-TRFT SYS-1027GR-TSF
RSC-R1UG-E16BR-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TQF SYS-1027GR-TQFT
RSC-R1UG-E16R+II 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-72R2 SYS-1027GR-72RT2 SYS-1027GR-TR2 SYS-1027GR-TRT2 SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16R-UP 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-1017GR-TF SYS-5017GR-TF SYS-1018GR-T SYS-5018GR-T
RSC-R1UG-E16R-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	1026GT-TRF SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF SYS-1027GR-TRF+ SYS-1027GR-TRFT SYS-1027GR-TRFT+ SYS-1027GR-TSF 1026GT-TSF
RSC-R1UG-E16S 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1022GG-TF 1122GG-TF
RSC-R1UG-UR 	GPU	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-UR-X9 	GPU	1U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R1UT-E16 	Twin	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-6016T-GTF SYS-6016T-GIBXF
												SYS-2027PR-HTR SYS-2027PR-DC1R 6027PR-DC0R SYS-2027PR-HC0R SYS-2027PR-DTR SYS-2027PR-DC0R 6027PR-DTR SYS-1028TP-DC0FR SYS-1028TP-DC0R SYS-1028TP-DC0TR 1028TP- DTTR/DC0TR/DC1TR SYS-1028TP-DC1TR

RSC-R1UTP-E16R-O-P

RSC-R1UU-E8PR 	UIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R1UU-E8R+ 	UIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: No gen3: No	No	No	No	No	No	1026T-6RF+ SYS-1026T-6RFT+ 1026T-URF4+ 1026T-URF4+-LR SYS-5017C-URF 6016T-6RFT+ 6016T-NTRF4+ 6016T-URF4+ 1011M-Ni 1011M-UR 1016I-UF 5015B-NTB 5015B-NTRB 5015B-UB 5015B-URB 5015M-Ni 5015M-NTR 5015M-NT 5015M-UR 5015M-U 5016I-NTF 5016I-URF 6016T-6RF+
RSC-R1UU-UE16 	UIO	1U	LHS	Passive	Output: (1) PCI-E x16 (1) UIO Signal: (1) PCI-E x16 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: Yes, depending on MB	Yes	No	No	No	Yes	AS-1022G-URF 1026T-UF 1026T-URF 1026T-URF4+ 1026T-URF4+-LR 1027B-URF SYS-5017C-URF 6016T-UF 6016T-URF 6016T-URF4+ 6017B-URF 6016T-U
RSC-R1UU-UE8 	UIO	1U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	1026T-6RF+ SYS-1026T-6RFT+ 6016T-NTF 6016T-NTRF 6016T-NTRF4+ 1011M-Ni 1011M-UR 5015B-NTB 5015B-NTRB 5015M-Ni 5015M-NTR 5015M-NT 5016I-NTF 6015B-Ni 6015C-Ni 6015C-NTR 6015C-NT 6015W-Ni 015W-NTR 6015W-NT 6016T-6RF+ 6016T-NT
RSC-R1UW-2E16 	WIO	1U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	1027R-72BRFTP 1027R-72RFTP 1027R-N3RF 1027R-WRF SYS-1027R-WRF4+ SYS-1027R-WRFT+ 5017R-WRF 6017R-72RFTP SYS-6017R-N3RF4+ SYS-6017R-N3RFT+ SYS-6017R-NTF SYS-6017R-WRF SYS-1018R-WC0R SYS-1028R-TDW SYS-1028R-WC1R SYS-1028R-WC1RT SYS-1028R-WMR SYS-1028R-WMRT SYS-1028R-WTNR SYS-1028R-WTNRT SYS-1028R-WTR SYS-1028R-WTRT SYS-5018R-WR SYS-6018R-TD8 SYS-6018R-TDW SYS-6018R-WTR SYS-6018R-WTRT SYS-1028U-E1CR4+ SYS-1028U-E1CRTP+ SYS-1028U-TNR4T+ SYS-1028U-TNRT+ SYS-1028U-TR4T+ SYS-1028U-TR4+ SYS-1028U-TRT+ SYS-1028UX-CR-LL1 SYS-1028UX-CR-LL2 SSG-6019P-ACR12L SYS-1029P-WT SYS-1029P-WTR SYS-1029P-WTRT SYS-6019P-WT SYS-6019P-WT8 SYS-6019P-WTR SYS-1029U-E1CR25M SYS-1029U-E1CR4 SYS-1029U-E1CR4T SYS-1029U-E1CRT SYS-1029U-E1CRTP SYS-1029U-E1CRTP2 SYS-1029U-TR25M SYS-1029U-TR4 SYS-1029U-TR4T SYS-1029U-TRT SYS-1029U-TRTP SYS-1029U-TRTP2 SYS-6019U-TN4R4T SYS-6019U-TN4RT SYS-6019U-TR25M SYS-6019U-TR4 SYS-6019U-TR4T SYS-6019U-TRT SYS-6019U-TRTP SYS-6019U-TRTP2 SYS-1019P-WTR SYS-5019P-WT SYS-5019P-WTR

RSC-R2UG-A2E16-A 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRFH SYS-2027GR-TRFHT
RSC-R2UG-A2E16-B 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRFH SYS-2027GR-TRFHT
RSC-R2UG-E16R-X9 	GPU	2U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-2027GR-TRF SYS-2027GR-TRFH SYS-2027GR-TRFHT SYS-2028GR-TRH SYS-2028GR-TRH SYS-2028GR-TRHT SYS-2028GR-TRT 2026GT-TF 2026GT-TRF 2026GT-TRF-FM407 2026GT-TRF-FM409 2026GT-TRF-FM475 2027GR-TRFT 2027GR-TSF
RSC-R2UG-E8G-X9 	GPU	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-2027GR-TRF 2027GR-TRFT 2027GR-TSF
RSC-R2UG-UR-X9 	GPU	2U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	No	
RSC-R2US-3E8R 	Standard	2U	LHS	Passive	Output: (3) PCI-E x8 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SSG-2027B-DE2R24L SSG-6037B-DE2R16L
RSC-R2UT-2E8R 	Twin	2U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	Yes	2026TT-DLIBQRF 2026TT-DLIBXRF 2026TT-DLRF 6026TT-D6IBQRF 6026TT-HDIBQRF 6026TT-HDIBXRF 6026TT-HDTRF 2122TC-DL6RF4
RSC-R2UT-3E8R 	Twin	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-2027TR-D70FRF SYS-2027TR-D70QRF SYS-2027TR-D70RF SYS-6027TR-D70FRF SYS-6027TR-D70QRF SYS-6027TR-D70RF SYS-6027TR-D71FRF SYS-6027TR-D71QRF SYS-6027TR-D71RF SYS-6027TR-DTRF SYS-6027TR-DTRF SYS-6027TR-DTRF SYS-6028TR-D72R SYS-6028TR-DTR
RSC-R2UT-E16R 	Twin	2U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	6026TT-GIBQRF 6026TT-GIBXRF 6026TT-GTRF
RSC-R2UT-E8E16R 	Twin	2U	RHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	6027TR-GTRF
RSC-R2UU-2E2E4R 	UIO	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (2) PCI-E x2 (1) PCI-E x4	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R2UU-2E4E8R 	UIO	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (2) PCI-E x4 (1) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	2026T-URF4+ 6026T-URF4+
RSC-R2UU-2E4R 	UIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x4	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-2E8 	UIO	2U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R2UU-2E8R 	UIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	2021M-UR+V 2021M-UR+B 6025W-URV 6025W-URB

RSC-R2UU-2U 	UIO	2U	LHS	Passive	Output: (2) UIO Signal: (2) UIO (PCI-E x8)	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R2UU-3E8G 	UIO	2U	LHS	Passive	Output: (3) PCI-E x16 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-A4E8+ 	UIO	2U	LHS	Active	Output: (4) PCI-E x8 Signal: (4) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R2UU-E8E16 	UIO	2U	LHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-U2E4E8G 	UIO	2U	LHS	Passive	Output: (1) PCI-E x16 (2) PCI-E x8 (1) UIO Signal: (2) PCI-E x4 (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	6027B-URF 2026T-URF4+ 6026T-URF4+
RSC-R2UU-UA3E8+ 	UIO	2U	LHS	Active	Output: (3) PCI-E x8 (1) UIO Signal: (3) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: No	No	No	No	No	No	AS -2022G-URF 2022G-URF4+ 6026T-UR 6026T-URF
RSC-R2UU-UE8 	UIO	2U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R2UW+-2E16-2E8 	WIO	2U	LHS	Passive	Output: (2) PCI-E x16 (2) PCI-E x8 Signal: (2) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027R-N3RFT+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+
RSC-R2UW-2E4R 	WIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x4	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UW-2E8E16 	WIO	2U	LHS	Passive	Output: (3) PCI-E x16 Signal: (1) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	6027R-72RFTP+ 2027R-72RFTP+
RSC-R2UW-2E8E16+ 	WIO	2U	LHS	Passive	Output: (2) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	SYS-6027R-CDNRT+ SYS-6027R-TDT+ SYS-6028R-TDWNR
RSC-R2UW-2E8R 	WIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	2027R-72RFTP+ SYS-2027R-N3RFT+ 6027R-72RFTP+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+ SYS-6028R-WTR SYS-6028R-WTRT
RSC-R2UW-4E8 	WIO	2U	LHS	Passive	Output: (4) PCI-E x8 Signal: (4) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	2027R-WRF SYS-5027R-WRF SYS-6027R-N3RF SYS-6027R-WRF SYS-2027R-N3RFT+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+ SYS-6028R-WTR SYS-6028R-WTRT
RSC-R2UW-E8R-UP 	WIO	2U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-5027R-WRF SYS-5028R-WR SYS-6027R-CDNRT+ SYS-6027R-TDT+ SYS-6028R-TDWNR
RSC-R2UW-U2E8 	WIO	2U	LHS	Passive	Output: (2) PCI-E x8 (1) UIO Signal: (2) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-RBL-E16 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	No	SBI-7127R-SH SBI-7427R-SH SBI-7426T-SH SBI-7126T-SH SBI-7126T-SL
RSC-RBL-E16LP 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	No	No	No	No	No	SBI-7427R-S2L SBI-7427R-S2L
												AS -1012G-MTF AS -1041A-T2F AS -1041M-T2+B 1042G-LTF AS -1042G-TF SYS-1017R-MTF

RSC-RR1U-E16 	Standard	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes, depending on MB gen3: Yes, depending on MB	No	No	No	No	Yes	SYS-1026T-M3 SYS-1027B-MTF SYS-5017R-MF SYS-5017R-MTF SYS-5017R-MTRF SYS-6016T-MR SYS-6016T-MT SYS-6016T-MTHF SYS-6016T-MTLF SYS-6016T-T SYS-6017B-MTF SYS-6017B-MTLF SYS-6017B-MTRF 6017R-TDAF SYS-6017R-TDF SYS-8016B-6F SYS-8016B-TF SYS-8016B-TLF SYS-8017R-7FT+ SYS-8017R-TF+ 1011M-T2 1041M-82 1041M-T2 1016I-M6F 1016T-M3FB 1018D-73MTF 1026T-T 1026T-TF 5015A-EHF 5016I-M6F 5016I-MT 5016I-MTF 5016I-MTH 5016I-MTHF 5016T-MRB 5016T-MRBB-LN4 5016T-MTFB 5016T-TB 5017P-TF 5017P-TLN4F 5018D-MF 5018D-MTLN4F 5018D-MTRF 6016T-TF 6017R-TDLRF 8014T-T 8014T-TB 8015C-TB
RSC-RR1U-E8 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on MB gen3: Yes, depending on MB	No	No	No	No	Yes	1012C-MRF AS -1021M-T2+V SYS-1017C-TF SYS-1027R-73DARF 1027R-73DBRF SYS-5017C-LF SYS-5017C-MF SYS-5017C-MTF SYS-5017C-MTRF SYS-5017C-TF SYS-5037MC-H86RF SYS-5037MC-H8TRF 5037MR-H8TRF 6016T-6F SYS-6017R-TDF+ 1012A-M73RF 1012A-MRF 1012A-MTF 1015B-3B 1015B-M3B 1016I-TF 1025C-3B 1025C-M3B 1027R-73DAF 5015B-M3B 5016I-MR 5016I-MRF 5016I-MRH 5016I-T 5016I-TF 5038ML-H8TRF 6015C-M3 6015C-M3B 6015C-MT 6015C-MT 6017R-M7RF 6017R-M7UF 6017R-MTLF SYS-5038MD-H8TRF SYS-5038ML-H8TRF SYS-5038MR-H8TRF SYS-6018R-MD SYS-6018R-MT SYS-6018R-MTR SYS-6018R-TD SYS-6018R-TDTP SYS-6018R-TDTPR SYS-5039MS-H8TRF
RSC-RR1U-HT 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8 + HT connector	gen2: No gen3: No	No	No	No	No	No	
RSC-U2N4-6 	Ultra	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	4	No	Yes	Yes	SYS-2028U-TN24RT+
RSC-UN4-88 	Ultra	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	4	No	Yes	Yes	SYS-1028U-TN10RT+
RSC-W-68 	WIO	1U	LHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	Yes	No	SYS-5019S-WR
RSC-W-88 	WIO	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (8) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-6028R-WTR SYS-1028R-WTR SYS-1028R-WC1R
RSC-W2-66					Output:							

	WIO	2U	LHS	Passive	(2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	SYS-6028UX-TR4 SYS-2048U-RTR4
---	-----	----	-----	---------	--	------------------------	-----	----	----	-----	-----	--