


## Socket pins for .055" Diameter Holes

R31, R52, R53

3A Current Rating, Brass alloy shell, sleeve & post.

Accepts .015" to .025" diameter leads



R31


- R31 • Three level wire wrap tail, .025" sq. posts
- Four-finger contacts; 10 micron gold flash over nickel plating on contacts and shell/sleeve/posts.
- Male pin/lead depth of 0.170"

- R52 • Three level wire wrap tail, .025" sq. posts
- Four-finger contacts; 10 micron gold flash over contacts.
- Tin plating on outer shell, sleeve & posts
- Male pin/lead depth 0.170"

- R53 • Three level wire-wrap tail, .025" sq. posts
- Six-finger contacts. 10 micron gold flash over contacts
- Tin plating on outer shell, sleeve & posts
- Male pin/lead depth of 0.170"

Part No. Pkg Qty  
R31/C 100  
R31/M 1000

Part No. Pkg Qty  
R52/C 100  
R52/M 1000  
R53/C 100  
R53/M 1000




R52-R53

Pins  
Terminals

## R32

Socket Pins for .042" diameter holes  
3A internal contact current rating  
Brass alloy shell, sleeve & post  
Accepts .015" to .025" diameter leads



R32

- Three-level wire-wrap tail, .025" square post
- Four-finger contacts
- 10 micron gold flash over nickel plating on contacts and shell/sleeve/posts
- Male pin/lead depth 0.130"

Use P158 Insertion Tool on Page 76  
D9 Die Point

Part No. Pkg Qty  
R32/C 100  
R32/M 1000



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vector](#):

[R32/C](#) [R31/C](#) [R52/C](#)