





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN
PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

REVISIONS
REV DESCRIPTION DATE CHANGED BY
G ECN 4564: ADDED ROHS, UPDATED DRAWING AND NEW FORMAT 3/3/10 D FRISIELLO
H ECN 5937: ADDED NOTE FOR PANEL MOUNTING 1/24/12 D FRISIELLO



NOTE: DIFFERENT STANOFFS AND JACK SCREWS
ARE REQUIRED FOR PANEL MOUNTING.
SEE WWW.L-COM.COM OR MASTER CATALOG FOR DETAILS.



NOTES:

MATERIAL:
SHELL: STEEL
CONTACTS: COPPER ALLOY
HARDWARE: BRASS
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)



FINISH:
SHELL: TIN/NICKEL PLATED
CONTACTS: GOLD FLASH PLATED
HARDWARE: NICKEL PLATED

ELECTRICAL:
CURRENT RATING: 3 AMP

MISCELLANEOUS:
OPERATING TEMPERATURE RANGE: -55 °C TO +105 °C.
ALL CONTACTS ARE WIRED STRAIGHT THROUGH.
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.
"GENDER CHANGER" FONT ARIAL BOLD, TEXT HEIGHTS: .085"
TEXT COLOR: WHITE.

PACKAGING:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (mm)

DIMENSIONAL
TOLERANCES:
X = ±.01
XX = ±.01
XXX = ±.005

ANGULAR TOLERANCES:
ALL = ± 1

PROJECTION

APPROVALS DATE
DRAWN BY 03/01/2002
CHECKED BY 11/08/2001
T.CLAIR

APPROVED BY 03/01/2002
R.CARICK

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

COLOR VARIATIONS
MAY OCCUR

Global Connectivity 45 BEECHWOOD DRIVE
NORTH ANDOVER, MA 01845

CATEGORY D-SUBMINIATURE

PRODUCT DESCRIPTION SOCKET SAVER, HD78 FEMALE/MALE

SIZE FSCM NO. DWG. NO. REV.
B 43321 DGBH78MF H

SCALE: 2:1 CAD FILE: DGBH78MF.SLDRW

SHEET 1 OF 1