





REV.	DATE	DESCRIPTION
NC	03/26/01	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"

	DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS	DATE	 Connex Connector Corporation			
1	BODY	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE 0.3-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-316 = ± 1 316-1000 = ± 1.6 1000-2000 = ± 2.4		DRAWN G.R.S.	03/26/01	TITLE PCB MOUNT CABLE TERMINAL (FOR RG-174/U, 188A/U, 316/U CABLE)			
2	FERRULE	COPPER	GOLD			CHECKED					
3						ISSUED					
4								SIZEFSOM NO.DWG. NO.142304.DWGREV. A99001142304.DWGNC			
5											
6											
7								SCALE NAA PART NO.142304SHEET1 OF 1			
8											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142304](#)