


AMP

WIRE RANGE

8 AWG

STRANDED



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°c	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± - MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: RED FINISH TIN PLATE PER MIL-T-10727	QTY	LOOSE PC	53041	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: - -		DR 6-18-93 S.S. GOULDEN	PACKAGE TYPE	AMP AMP Incorporated Harrisburg, PA 17105-3608	
					CHK 6-18-93 R. HERSEY			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] STRANDED		APPD 6-18-93 B. BARE	NAME	TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 8 AWG	
					APPD 6-18-93 M. ELLIS			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
				APPLICATION SPEC	B	00779	C=53041	
				WEIGHT -	SCALE	NTS	SHEET	1 OF 1