


## ASSERTA 24 VOLT HIGH OUTPUT SOUNDER / BEACON



The Asserta Industrial warning sounder / beacon is designed to cope with harsh environments requiring protection to IP66. Design features are incorporated to ensure safer and easier installation, while providing flexibility with fewer product variants.

- 24Vdc OPERATION
- 110dB(A) OR 120dB(A) OUTPUT VERSION AVAILABLE
- IP66 PROTECTION
- FULLY INTEGRATED ASYMMETRIC BEACON USES LIGHT MORE EFFICIENTLY
- SIMPLE FIRST & SECOND FIX INSTALLATION
- 42 ALARM TONES
- 3 STAGE ALARM
- SOUNDER TIME OUT - USER ADJUSTABLE
- OPTIONAL SWIVEL MOUNT BRACKET

## Specification

|                   |                                           |
|-------------------|-------------------------------------------|
| Voltage           | 18 - 30Vdc                                |
| Current           | 110dB(A) = 320mA    120dB(A) = 650mA      |
| Output @ 1m       | 110dB(A)    120dB(A)                      |
| Tones             | 42                                        |
| Alarm Stages      | 3                                         |
| Flash Rate        | 0.75 / 1.0 / 1.25 / 2Hz (user selectable) |
| Flash Power       | 3.6j (typ)                                |
| Temperature       | - 20°C to + 70°C                          |
| Construction Body | PC / ABS                                  |
| Construction Lens | Polycarbonate                             |
| IP Rating         | IP66                                      |
| Weight            | 1.8Kg                                     |
| Body Colour       | Red or Grey                               |
| Lens Colour       | Red, Amber or Clear                       |