




PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT
	MIN. in (mm)	MAX. in (mm)												
PLUP40S	.197 (5)	1.57 (40)	.047 (1.2)	.190 (4.8)	.295 (7.5)	.744 (18.9)	.320 (8.1)	6.97 (177)	.378 (9.6)	.266 (6.8)	.050 (1.3)	50 (222)	STANDARD	.31 (141)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PLUP40S
UMBRELLA WINGED PUSH MOUNT CABLE TIE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(.25) (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

9	11/24/04	ERW		CHANGED MIN. LOOP TENSILE TO 50 (222mm).	27066	9				
8	11/1/04	JABO	JVL	CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS	27066	8	JVL			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

DRAWN BY
BSH

DATE
11/13/96

CHK'D
JML

MAT'L:

NYLON
6.6

SCALE
NONE

DRAWING NO.
SS-27066

DWG
A
SIZE