

PTFE TEST POINT JACKS

PTFE COLOR CHART

XX	COLOR
10	BLACK
11	BROWN
12	RED
13	ORANGE
14	YELLOW
15	GREEN
16	BLUE
17	VIOLET
18	GRAY
*19	WHITE

* STANDARD

1128-XX- XX XX

BASIC PART NUMBER

FINISH

COLOR (SEE COLOR CHART)




FIG. 2




FIG. 3




FIG. 4




FIG. 5




FIG. 5A




FIG. 6




FIG. 7




FIG. 8




FIG. 9

PART NO.	FIG.	A	B	C	D	E	F††	G	H*	N	P	R	T
1128-33	2	.218	.185	.700	.046	-	.896	.054	.050			.070	.300
34	3	.172	.148	.204	.046	.175	.425	.040	.032	.020	.060	.080	.200
35	4	.218	.184	.284	.046	.105	.435	.080	.080	.020	.065	.125	.310
36	5	.172	.148	.175	.046	.187	.408	.060	.040				.135
37	4	.172	.148	.424	.046	.187	.657	.062	.040	.015	.161	.093	.400
50	6	.219	.185	.316	.062	.233	.385	.050	.080	.125		.080	.250
51	7	.218	.187	.689		.140	.500	.050	.080	.125		.080	.500
52	7	.218	.187	.378		.140	.400	.050	.080	.125		.080	.250
53	7	.218	.187	.378		.140	.400	.035	.080	.187		.080	.250
54	7	.218	.187	.378		.140	.500	.050	.080	.125		.080	.250
55	7	.218	.187	.398		.140	.520	.040	.080	.130		.080	.270
56	8	.250	.218	.316	.062	.250	.500	.050	.080	.125		.080	.250
57	8	.250	.218	.316	.062	.250	.400	.050	.080	.125		.080	.250
58	5A	.218		.430		.150	.580	.050	.080				.200
59	5A	.218		.500		.150	.650	.050	.080				.280
65	9	.172	.148	.204	.046	.150	.400	.040*	.033				.200
66	9	.250	.218	.318	.060	.176	.554	.040	.080				.250

TERMINAL JACK : (BERYLLIUM COPPER CONTACTS) GOLD PLATED
BUSHING : PTFE

*=±.001

††= REFERENCE DIMENSION