



1500W Modified Sine Wave DC-AC Power Inverter **A-301/302-1K7** series



■ Features :

- 12V or 24V DC input
- Power ON-OFF switch
- Input voltage range: -15% ~ +25%
- Output voltage regulation: ±10%
- Protections: Bat. Low alarm/Bat. Low shutdown/Over voltage/Over temp./Output short/Input polarity reverse/Over load.
- Output waveform: Modified sine wave
- Cooling fan ON-OFF control
- ON/OFF remote control(Optional)
- Approvals: e13/ CE
- 1 year warranty



SPECIFICATION

ORDER NO.	A301-1K7-B2	A301-1K7-F3	A302-1K7-B2	A302-1K7-F3
OUTPUT	SAFETY MODEL NO. A-1700W			
	AC VOLTAGE	110V	230V	110V
	RATED POWER	1500W		230V
	PEAK POWER	1700W 30min.		
	SURGE POWER	3000W		
	WAVEFORM	Modified Sine Wave		
	FREQUENCY	60Hz±1%	50Hz±1%	60Hz±1%
	AC REGULATION	±10%		±10%
	STANDARD RECEPTACLES	TYPE-2* 3ea	TYPE-3* 2ea	TYPE-2* 3ea
INPUT	LED INDICATOR	Green LED for power on; Red LED for power failure status		
	DC CURRENT	170A		85A
	NO LOAD CURRENT DRAW	0.6A		0.36A
	DC VOLTAGE	12V		24V
	VOLTAGE RANGE	10 ~ 15VDC		21 ~ 30VDC
	EFFICIENCY (Typ.)	82%		85%
	DC CONNECTOR	1000mm R type terminal		1000mm R type terminal
	FUSE	30A*10		20A*10
PROTECTION	BAT. LOW ALARM	10±0.5V		21±0.8V
	BAT. LOW SHUTDOWN	9.5±0.5V		20±0.8V
	OVER LOAD	>1700W shut down o/p voltage, re-power on to recover		
	OVER VOLTAGE	15 ~ 16V		29 ~ 31V
	OVER TEMPERATURE	60±5°C / 140±9°F		
	OUTPUT SHORT	Shut-off		
	BAT. POLARITY	By fuse open		
ENVIRONMENT	WORKING TEMP.	0 ~ 30°C @ 100% load, 40°C @ 70% load		
	WORKING HUMIDITY	20% ~ 90% RH non-condensing		
	STORAGE TEMP., HUMIDITY	-30 ~ +70°C / -22 ~ +158°F, 10 ~ 95% RH		
	TEMP. COEFFICIENT	±0.05% / °C (0 ~ 50°C)		
SAFETY & EMC	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH		
	EMI CONDUCTION & RADIATION	Compliance to EN55022 class B, 72/ 245/ CEE, 95/ 54/ CE		
	EMS IMMUNITY	Compliance to EN61000-4-2,3		
	LVD	Compliance to EN60950		
OTHERS	MTBF	86852Khrs min. MIL-HDBK-217F (25°C)		
	DIMENSION	455*210*85mm (L*W*H)		
	PACKING	5.5kg; 3pcs / 19.6kg / CARTON		
	COOLING	>40°C (NTC) fan on		
	APPLICATIONS	Home appliance, Power tools, Office and Portable equipment and Vehicle ...etc.		

■ AC Output Receptacles (optional)

TYPE-1	TYPE-2	TYPE-3	TYPE-4	TYPE-5	TYPE-6
JAPAN	USA	EUROPE	UNIVERSAL	AUSTRALIA	U.K



1500W Modified Sine Wave DC-AC Power Inverter **A-301/302-1K7** series

■ Mechanical Specification

Unit:mm

