


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	LEGEND	HEIGHT "A"	WIDTH "B" (+/- .062)	LEGEND HEIGHT "C"	COLOR (LEGEND/ BACKGROUND)	MARKERS PER CARD	STD. PKG. QTY. CARD(S)
5 PVL100BY-0-Y	0	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
5 PVL100BY-1-Y THRU PVL100BY-9-Y	1 THRU 9	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
5 PVL100BY-A-Y THRU PVL100BY-Z-Y	A THRU Z	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
PVL100BY-DSH-Y	- (DASH)	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
5 PVL200BY-0-Y	0	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
5 PVL200BY-1-Y THRU PVL200BY-9-Y	1 THRU 9	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
5 PVL200BY-A-Y THRU PVL200BY-Z-Y	A THRU Z	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
PVL200BY-DSH-Y	- (DASH)	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25

NOTE:  
1. MILLIMETERS ARE IN [     ].



CAD FILENAME/LAYERS I00569AK - DC - C10500/06F	
PANDUIT CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING VINYL LETTERS AND NUMBERS PVL100BY-*** AND PVL200BY-***	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12    (.XXX) ± .025 (.XX) ± .062    ANGLES ± 5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
5 1/14/11 JHAC <i>JHAC</i> Width should be .900" and legend height for the 1200 parts should be 2", not 1". UPDATE TABLE. ADD 9.25 WIDTH.	DRAWN BY RVU
4 04/29/09 JHAC CHANGED TOLERANCE ON DIM "B" TO +/- .062	DATE 9-15-06
REV DATE BY CHK DESCRIPTION ECN - R CUST SUP	CHK'D <i>JHAC</i>
MAT'L: GMVI-OL FILM VINYL	
SCALE NTS	DWG A SIZE
DRAWING NO. C10500	