

Ratings:

Current	16A
Voltage	300 VB
Wire Size	28-14AWG
Test Voltage	2.0 kV

Rated Cross Section:

Single Wire (solid)	2.5mm ²
Stranded Wire (flexible)	2.5mm ²
Stranded Wire with Ferrules	1.5mm ²

Dimensions:

Spacing	5.0mm(5.08mm)
PCB Hole Diameter	1.0mm(2x)
Stripped Length	6.0mm

Materials:

Insulating Material	PA
Flammability	UL94V-0
Temperature	-30°C/+105°C
Cage Clamp	Stainless Steel
Wire Guard	Cu
Color	Slade Gray

