

16,24 and 40 Column Impact Type

M150 Series

EPSON



- Low power impact printer range
- 5V DC operation
- Choice of 2 paper widths

Specification:	M150	M160	M164
Order Code	308-122	308-134	308-146
Printer type	16 column impact	24 column impact	40 column impact
Print speed	1 line/sec	0.7 lines/sec	0.4 lines/sec
Weight	60g	75g	75g
Paper width	44mm	57mm	57mm
Operating voltage	5V dc	5V dc	5V dc
Current consumption	1A peak	1A peak	1A peak
Operating temperature	0 to +50°C		
Dimensions	H=12.8, W=73.4, D=42.6	H=12.8, W=91, D=42.6	

234179

Printers	Mfrs. List No.	Order Code	Price Each
16 Column	M150	308-122	
24 Column	M160	308-134	
40 Column	M164	308-146	
Consumables			
Ribbon for M160/M164 (Black)		440-8172	
Paper roll for M150 (x 20)		101-3707	
Paper roll for M160/M164 (x 20)		101-3721	