


PRODUCTS

- Large Cabinet Racks
- Communications Cabinets/Racks
- Cabinets
- Open Racks
- Chassis
- Small Metal Enclosures
- Die Cast Boxes
- Plastic Boxes
- NEMA Boxes (Water-tight Plastic and Fiberglass)
- NEMA Boxes (Water-tight Sheet Metal)
- NEMA Boxes (Water-tight Aluminum)
- Accessories
- Brackets
- Custom Products

Plastic Boxes
Plastibox
Style D



Click on Image for Larger View

Available in a variety of styles and sizes, these functional utility enclosures are made from UL rated high impact plastics with a scratch resistant finish.

Design Features

Contact BUD factory for optional colors, materials, EMI/RFI shielding and custom modifications. Styles C&D have rounded corners and edges and come with four non feet. Interior is plain with no molded - in PCB mounting allowing for more usable space. Optional universal mounting bosses are available (see optional accessories) PC Bone Gray Polystyrene plastic. UL94 - HB flammability rating.

Finishes

Available in two types of finishes and with or without battery compartments, refer to the following prefix description to insure proper ordering.

PS - Textured body with smooth insert.

PT - Textured body with textured top.

PBS - Textured body with smooth top insert and 9 - volt battery compartment.

PSS - Textured body with smooth top and end panels.

PSP - Textured body with smooth top and sloped panels.

PBSP - Textured body with smooth top, and sloped panel, and battery compartment.

Plastibox												
Catalog No.	Drawing	Style	A	B	C	D	E	F	G	H	I	Wgt. Ozs.
PT-11308	PDF DXF	A	3.62'	2.25'	1.50'	N/A	.70"	3.32'	1.94'	1.30'	N/A	2.5
PBS11327	PDF DXF	A	5.62'	3.25'	1.50'	N/A	.70"	5.32'	2.94'	1.30'	N/A	4.5
PS11339	PDF DXF	A	9.50'	6.34'	1.50'	N/A	.70"	9.19'	6.03'	1.30'	N/A	8.5
PT-11372	PDF DXF	A	3.62'	2.25'	2.50'	N/A	.70"	3.29'	1.94'	2.30'	N/A	3.0
PT-11388	PDF DXF	A	5.62'	3.25'	2.48'	N/A	.70"	5.32'	2.94'	2.28'	N/A	5.0
PS11292	PDF DXF	B	5.62'	3.25'	1.50'	.98"	.70"	5.32'	2.94'	1.20'	.78"	3.5
PBS11294	PDF DXF	B	5.62'	3.25'	1.50'	.98"	.70"	5.32'	2.94'	1.20'	.78"	4.0
PSS11350	PDF DXF	B	6.88'	4.88'	2.45'	1.54'	.70"	6.48'	4.48'	2.25'	1.34"	6.5
PBS11273	PDF DXF	C	6.30'	3.75'	1.41'	N/A	.75"	6.08'	3.53'	1.14'	N/A	5.0
PS11276	PDF DXF	C	6.30'	3.75'	1.41'	N/A	.75"	6.08'	3.53'	1.14'	N/A	5.0
PBS11275	PDF DXF	D	6.30'	3.75'	1.41'	1.13'	.75"	6.08'	3.53'	1.14'	8.76"	5.0
PS11279	PDF DXF	D	6.30'	3.75'	1.41'	1.13'	.75"	6.08'	3.53'	1.14'	8.76"	5.0
PS11502	PDF DXF	E	5.27'	7.44'	2.15'	1.27'	.75"	4.94'	7.10'	1.98'	1.10"	7.8
PS11505	PDF DXF	E	7.44'	5.27'	2.15'	1.27'	.75"	7.10'	4.94'	1.98'	1.10"	7.8
PS11521	PDF DXF	F	3.62'	2.25'	1.01'	N/A	.72"	3.32'	1.94'	.81"	N/A	2.0
PBS11532	PDF DXF	F	4.37'	3.25'	1.52'	N/A	.70"	4.07'	2.94'	1.32'	N/A	3.5
PS11533	PDF DXF	F	4.37'	3.25'	1.52'	N/A	.70"	4.07'	2.94'	1.32'	N/A	3.5
PS11543	PDF DXF	F	5.62'	3.25'	1.52'	N/A	.71"	6.57'	4.57'	1.32'	N/A	4.0
PS11553	PDF DXF	F	6.87'	4.87'	1.52'	N/A	.71"	6.57'	4.57'	1.32'	N/A	6.5
PT-11557	PDF DXF	F	6.87'	4.87'	2.52'	N/A	.71"	6.57'	4.57'	2.32'	N/A	8.5
PSP11563	PDF DXF	G	5.90'	3.74'	1.93'	1.12'	.56"	5.66'	3.50'	1.66'	.85"	5.1
PSP11572 +	PDF DXF	G	7.49'	4.14'	2.31'	1.32'	.71"	7.25'	3.90'	2.11'	1.05"	7.2
PSP11573	PDF DXF	G	7.49'	4.14'	2.31'	1.32'	.71"	7.25'	3.90'	2.11'	1.05"	7.0
PT-11642	PDF DXF	H	4.25'	2.62'	1.25'	N/A	.65"	4.05'	2.42'	1.05'	N/A	2.9
PT-11643	PDF DXF	H	5.62'	3.25'	1.12'	N/A	.65"	5.42'	3.05'	.92"	N/A	3.7
PT-11644	PDF DXF	H	6.00'	4.00'	1.12'	N/A	.65"	5.80'	3.80'	.92"	N/A	4.3
+ with battery compartment												

Perimeter Gas	Drawing	Fits Catalog Numbers
PG-1172	N/A	PS11301, PT11308, PT11372
PG-1176	N/A	PS11325, PBS11327, PT11388, PS11298 PS11290, PS11292, PBS11294

[DXF](#)Autocad DXF Specifications File
(Requires CAD software such as AutoCAD)

[PDF](#)Adobe PDF Specifications File



[Download PDF Viewer](#)