


Splices (Continued)

**Side Feed Splices —
Non-Insulation Support**


Type	Wire Range		Stock Thickness	Crimp Width	Dim. L	Material	Part Number
	CMA	mm ²					
A	400-1300	0.20-0.66	.016	.070	.100	Brass	62759-1
			0.41	1.78	2.54	Tin Plated Brass	62759-2
						Steel	62759-5
	500-2200	0.25-1.11	.030	.110	.100	Brass	485016-1
			0.76	2.79	2.54		
	1200-2600	0.61-1.32	.020	.090	.120	Brass	61769-1
					3.05	Nickel Plated Steel	61769-2
					.190	Brass	60372-1
					4.83		
	1500-5000	0.76-2.53	.020	.110	.155	Brass	63130-2
					3.94	Tin Plated Brass	63130-3
						Tin Plated Phos. Bz.	63130-4
						Brass	485043-1
	4000-9000	2.03-4.56	.020	.140	.250	Tin Plated Brass	485043-2
					6.35	Nickel Plated Steel	485043-4
						Tin Plated Steel	61299-1
	7000-12500	3.55-6.33	.031	.180	.265	Tin Plated Brass	61299-2
					6.73	Brass	61299-3
	8500-14000	4.31-7.10	.025	.180	.265	Brass	1217967-1
					6.73	Tin Plated Brass	1217967-2
	14000-30000	7.10-15.20	.030	.280	.310	Brass	62754-1
					7.87	Tin Plated Brass	62754-2

Splices