



Search Results

Evaluate

- FAQ's
- Line Cards
- PDF-NetKey Cabli ..

Design a Solution

- Part Drawings
- PDF-NetKey Fiber ..
- Specification Sheets
- PDF-NetKey Fiber ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'NKFLCSSWH'

Your search criteria matched only one product, shown below

NKFLCSSWH



- Meets TIA/EIA-568-B.3 requirements
- Insertion loss: .1dB typical (multimode), .2dB typical (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Field polish termination -- Panduit recommends anaerobic adhesive
- Use Field Polish Termination Kit (FIELDKIT)

▪ Part Number	NKFLCSSWH
▪ RoHS Compliancy Status	Compliant
▪ Part Description	NetKey® LC Singlemode Simplex Connector, Blue (BU) body, White (WH) boot.
▪ Product Type	NetKey® Network Components
▪ Boot Color	White (WH)
▪ Pricing Description	Netkey LC Singlemode Simplex Connector (BU Body WH Boot)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.