

Data Sheet

SP043xxVBNN

(ASP043)


Page 1/4

Order Number

ASP043xx

xx=number of poles

Illustration



see enlarged drawing at the end of the document

Product specification

- spring clamp terminal block, pluggable
- centerline 3.50 mm, direction of connection vertical (0°)
- color black
- eccentric lever, wire entry undecodeable side parallel to plug direction

Data Sheet

SP043xxVBNN

(ASP043)

Page 2/4
Order Number
ASP043xx
xx=number of poles

Technical Data

General Data

min. number of positions	2		
max. number of positions	12		
Insulating material class	CTI 400		
clearance/creepage dist.	2.3 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	320 V	320 V
Stossspannung	2.5 kV	4 kV	2.5 kV

Connection data

rat. wiring solid AWG/mm ² min-max	AWG 28/0.08 mm ² - AWG 16/1.5 mm ²
rat. wiring strand AWG/mm ² min-max	AWG 28/0.08 mm ² - AWG 16/1.5 mm ²

Material

insulating material	PA46
flammability class	V0

Climatic properties

Data Sheet

SP043xxVBNN

(ASP043)

Page 3/4

Order Number

ASP043xx

xx=number of poles

upper limit temperature	105 °C
-------------------------	--------

lower limit temperature	-40 °C
-------------------------	--------

General

tolerance	ISO 2768 -mH
-----------	--------------

Matching Part

311881	Type 188
--------	----------

311891	Type 189
--------	----------

313421	Typ 342
--------	---------

313431	Typ 343
--------	---------

Accessories

700025-01-9	Kodierstern weiß
-------------	------------------

Data Sheet

SP043xxVBNN

(ASP043)

Page 4/4


Order Number

ASP043xx

xx=number of poles

Illustration

Drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 4$ [0.157]