

Reset All Search

If you have questions please contact Technical Support. Riser Card naming convention (*) Device support limited; hardware monitoring of device may not be supported.
Note: Riser cards for SuperBlade and MicroBlade are sold with complete systems only.

Model	Category Any	Form Factor Any	Slot Position Any	Design Type Any	Output Type Any	Gen2 Any / Gen3 Any	GPU_PHI Support (*) Any	NVMe (or #Ports) Any	M.2 (or #Ports) Any	Thermal Sensor Any	Auto Detect Any	Systems
RSC-88-F1  Used together with RSC-88-F2 only	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-F618H6-FTL+ SYS-F618H6-FTPTL+ SYS-F618H6-FT+ SYS-F618H6-FTPT+
RSC-88-F2  Used together with RSC-88-F1 only	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-F618H6-FTL+ SYS-F618H6-FTPTL+ SYS-F618H6-FTPT+ SYS-F618H6-FT+
RSC-B-A6 	Super Blade	1U	LHS	Active	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-BLG-E16 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SBI-7126TG SBI-7127RG
RSC-BLG-E16LP 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	No	No	No	No	No	SBI-7126TG
RSC-BLG-E16R 	Super Blade	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: () PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SBI-7126TG SBI-7127RG
RSC-F2F-6 	FatTwin	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-F628G2-FC0+ SYS-F628G2-FC0PT+ SYS-F628G2-FT+ SYS-F628G2-FTPT+ SYS-F628G3-FC0+ SYS-F628G3-FC0PT+ SYS-F628G3-FT+ SYS-F628G3-FTPT+
RSC-G-6 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-G2F-A66 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	2028GR-TR 2028GR-TRH 2028GR-TRHT 2028GR-TRT
RSC-G2FR-A66 	GPU	2U	RHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	2028GR-TR 2028GR-TRH 2028GR-TRHT 2028GR-TRT
RSC-GR-6 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: gen3:	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-GR-A88 	GPU	1U	RHS	Active	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	1028GQ-TR 1028GQ-TRT
RSC-MLP-E8R 	MLP	1U	RHS	Passive	Output: (1) Micro LP Signal: () Micro LP	gen2: Yes gen3: Yes	No	No	No	No	No	AOM-CGP-I2M AOM-CIBF-M1M AOM-CTG-I1SM
												SYS-5028TK-HTR SYS-2028TP-HC0R-SIOM SYS-2028TP-HC1R-SIOM SYS-2028TP-HTR-SIOM SYS-6028TP-HC0R-SIOM SYS-6028TP-HC1R-SIOM SYS-6028TP-HTR-SIOM

RSC-P-6 	TwinPro	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-6028BT-HNC0R+ SYS-2028BT-HNC0R+ SYS-2028BT-HNC1R+ SYS-2028BT-HNR+ SYS-2028BT-HTR+ SYS-6028BT-HNC0R+ SYS-1029TP-DC0R SYS-1029TP-DC1R SYS-1029TP-DTR SYS-2029TP-HC0R SYS-2029TP-HC1R SYS-2029TP-HTR SYS-6029TP-HC0R SYS-6029TP-HC1R SYS-6029TP-HTR SYS-2029BT-HNC0R SYS-2029BT-HNC1R SYS-2029BT-HNR SYS-2029BT-HNTR SYS-2029BT-HTR SYS-6029BT-HNC0R SYS-2028BT-HNTR+
RSC-R1U-33 	Standard	1U	LHS	Passive	Output: (1) PCI Signal: (1) PCI-32 (33 MHz)	gen2: No gen3: No	No	No	No	No	No	5017A-EF
RSC-R1U-E16R 	Twin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	1022GG-TF 1122GG-TF 2022TC-HTRF4 2022TG-H6RF AS -2022TG-HIBQRF AS -2022TG-HLIBQRF AS -2022TG-HTRF 2122TC-H6RF4 2122TG-H6IBQRF AS -2122TG-HTRF AS -2022TC-BTRF AS -1021TM-INF+B 1021TM-T+B SYS-1017GR-TF SYS-1026GT-TF SYS-1027TR-TFF SYS-1027TR-TQF 2016Ti-HTRF SYS-2027TR-H70FRF SYS-2027TR-H70QRF SYS-2027TR-H70RF SYS-2027TR-H71FRF SYS-2027TR-H71QRF SYS-2027TR-H71RF SYS-2027TR-H72FRF SYS-2027TR-H72QRF SYS-2027TR-H72RF SYS-2027TR-HTFRF SYS-2027TR-HTQRF SYS-2027TR-HTRF SYS-5017GR-TF 6016GT-TF SYS-6016TT-IBQF SYS-6016TT-IBXF SYS-6016TT-TF SYS-6017TR-TF SYS-6017TR-TFF SYS-6017TR-TQF SYS-6027TR-H70FRF SYS-6027TR-H70QRF SYS-6027TR-H70RF SYS-6027TR-H71FRF SYS-6027TR-H71QRF SYS-6027TR-H71RF SYS-6027TR-HTFRF SYS-6027TR-HTQRF SYS-6027TR-HTRF 1022TC-IBQF 1022TC-TF 2021TM-BIBXRF 2021TM-BTRF 1025TC-10GB 1025TC-3FB 1025TC-TB 1026TT-IBQF 1026TT-IBXF 1026TT-INFF 1026TT-TF 2026TT-H6IBQRF 2026TT-H6IBXRF 2026TT-H6RF 2026TT-HIBQRF 2026TT-HIBXRF 2026TT-HTRF 5015TB-10GB 5015TB-TB 5016Ti-TF 5026Ti-BTRF 5026Ti-HTRF 6015TC-10GB 6015TC-LFTB 6015TC-TB 6015TW-INF 6015TW-T 6016TT-INFF 6026TT-BIBQF 6026TT-BIBQRF 6026TT-BIBXF 6026TT-BIBXRF 6026TT-BINFF 6026TT-BINFRF 6026TT-BTF 6026TT-BTRF 6026TT-H6IBQRF 6026TT-H6IBXRF 6026TT-H6RF 6026TT-HIBQF 6026TT-HIBQRF 6026TT-HIBXF 6026TT-HIBXRF 6026TT-HTF 6026TT-HTRF 6026TT-IBQF 6026TT-IBXF 6026TT-TF
RSC-R1U-E8R 	Twin	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	6015T-T 6015T-INF

RSC-R1U-UL 	Standard	1U	LHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R1U-UT 	Twin	1U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: No gen3: No	No	No	No	No	No	
RSC-R1UEP-UE 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x4 (1) UIO (PCI-E x8)	gen2: No gen3: No	No	No	No	No	No	6015X-3V 6015X-3B
RSC-R1UF-E16R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-F617R2-R72+ SYS-F617R2-RT+ SYS-F618R2-R72+ SYS-F618R2-R72PT+ SYS-F618R2-RC0+ SYS-F618R2-RC0PT+ SYS-F618R2-RC1+ SYS-F618R2-RC1PT+ SYS-F618R2-RT+ SYS-F618R2-RTN+ SYS-F618R2-RTPT+ SYS-F618R2-RTPTN+
RSC-R1UFF-E16 	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	F617H6-FT+ F617H6-FTPT+ F617R2-F72+ SYS-F617R2-F73 SYS-F617R2-FT SYS-F617R2-FT+ SYS-F617R2-FTPT+ F617R3-FT SYS-F617R3-FT+ SYS-F617R3-FTPT+ F618R2-FC0 SYS-F618R2-FT F618R3-FTL F627R2-F73 F628R2-FC0
RSC-R1UFF-E16R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-F627R3-FT SYS-F627R3-F73 F628R3-FC0 F628R3-FT
RSC-R1UFF-E8 	FatTwin	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	F617H6-FTL+ F617H6-FTPTL+ SYS-F618R2-FT+ SYS-F618R2-FTPT+ SYS-F618R3-FT+ SYS-F618R3-FTPT+
RSC-R1UFF-E8R 	FatTwin	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	5017R-iHDP SSG-5018A-AR12L SYS-6017R-73HDP+ SYS-6017R-73THDP+ MNL-F517H6-FT F617H6-FT+ F617H6-FTL+ F617H6-FTPT+ F617H6-FTPTL+ F617R2-F72+ SYS-F617R2-FT+ SYS-F617R2-FTPT+ SYS-F618R3-FT+ SYS-F618R3-FTPT+
RSC-R1UG-2E8AR+II 	GPU	1U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	
RSC-R1UG-2E8G 	GPU	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	SYS-6016XT-TF
RSC-R1UG-2E8G-UP 	GPU	1U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-2E8GR-UP 	GPU	1U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-A2E16-X9 	GPU	1U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TRF+ SYS-1027GR-TRFT+
RSC-R1UG-E16 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-1026GT-TF 6016GT-TF
RSC-R1UG-E16-UP 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1017GR-TF SYS-5017GR-TF SYS-1018GR-T SYS-5018GR-T


RSC-R1UG-E16-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-1027GR-TRF+ SYS-1027GR-TRFT+ SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16A 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1026GT-TRF 1026GT-TRF-FM307 1026GT-TSF
RSC-R1UG-E16A+II 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-72R2 SYS-1027GR-72RT2 SYS-1027GR-TR2 SYS-1027GR-TRT2
RSC-R1UG-E16A-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-1027GR-TQF 1027GR-TQF-FM409 1027GR-TQF-FM475 SYS-1027GR-TQFT SYS-1027GR-TRF 1027GR-TRF-FM309 1027GR-TRF-FM375 SYS-1027GR-TRFT SYS-1027GR-TSF
RSC-R1UG-E16AR+II 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TR2 SYS-1027GR-TRT2 SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16AR-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	1026GT-TRF SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF SYS-1027GR-TRF+ SYS-1027GR-TRFT SYS-1027GR-TRFT+ SYS-1027GR-TSF 1026GT-TRF
RSC-R1UG-E16B 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1026GT-TRF 1026GT-TSF
RSC-R1UG-E16B-X9 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF 1027GR-TRF-FM309 SYS-1027GR-TRFT SYS-1027GR-TSF
RSC-R1UG-E16BR-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-TQF SYS-1027GR-TQFT
RSC-R1UG-E16R+II 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1027GR-72R2 SYS-1027GR-72RT2 SYS-1027GR-TR2 SYS-1027GR-TRT2 SYS-1028GR-TR SYS-1028GR-TRT
RSC-R1UG-E16R-UP 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-1017GR-TF SYS-5017GR-TF SYS-1018GR-T SYS-5018GR-T
RSC-R1UG-E16R-X9 	GPU	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	1026GT-TRF SYS-1027GR-TQF SYS-1027GR-TQFT SYS-1027GR-TRF SYS-1027GR-TRF+ SYS-1027GR-TRFT SYS-1027GR-TRFT+ SYS-1027GR-TSF 1026GT-TSF
RSC-R1UG-E16S 	GPU	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	1022GG-TF 1122GG-TF
RSC-R1UG-UR 	GPU	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R1UG-UR-X9 	GPU	1U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R1UT-E16 	Twin	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	SYS-6016T-GTF SYS-6016T-GIBXF
												SYS-2027PR-HTR SYS-2027PR-DC1R 6027PR-DC0R SYS-2027PR-HC0R SYS-2027PR-DTR SYS-2027PR-DC0R 6027PR-DTR SYS-1028TP-DC0FR SYS-1028TP-DC0R SYS-1028TP-DC0TR 1028TP-DTTR/DC0TR/DC1TR SYS-1028TP-DC1TR

RSC-R1UTP-E16R-O-P 	TwinPro	1U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-1028TP-DTFR 1028TP-DTR/DC0R/DC1R SYS-1028TP-DTTR SYS-1028TR-TF SYS-2027PR-HC0FR SYS-2027PR-HC0R SYS-2027PR-HC0TR SYS-2027PR-HC1FR SYS-2027PR-HC1R SYS-2027PR-HC1TR SYS-2027PR-HTFR SYS-2027PR-HTR SYS-2027PR-HTTR SYS-2028TP-HC0FR SYS-2028TP-HC0R SYS-2028TP-HC0TR SYS-2028TP-HC1FR SYS-2028TP-HC1R SYS-2028TP-HC1TR SYS-2028TP-HTFR SYS-2028TP-HTR SYS-2028TP-HTTR SYS-2028TR-H72FR SYS-2028TR-H72R SYS-2028TR-HTFR SYS-2028TR-HTR SYS-6018TR-T SYS-6018TR-TF SYS-6027PR-HC0FR SYS-6027PR-HC0R SYS-6027PR-HC0TR SYS-6027PR-HC1FR SYS-6027PR-HC1R SYS-6027PR-HC1TR SYS-6027PR-HTFR SYS-6027PR-HTR SYS-6027PR-HTTR SYS-6028TP-HTTR SYS-6028TP-HTR SYS-6028TP-HC0FR SYS-6028TP-HC0R SYS-6028TP-HC0TR SYS-6028TP-HC1FR SYS-6028TP-HC1R SYS-6028TP-HC1TR SYS-6028TP-HTFR SYS-1028TP-DC0FR SYS-1028TP-DC0R SYS-1028TP-DC0TR SYS-1028TP-DC1FR SYS-1028TP-DC1TR SYS-1028TP-DTFR SYS-1028TP-DTTR SYS-1028TR-T SYS-1028TR-TF SYS-2028BT-HNC0R+ SYS-2028BT-HNC1R+ SYS-2028BT-HNR+ SYS-2028BT-HTR+ SYS-2028TP-HC0R-SIOM SYS-2028TP-HC1R-SIOM SYS-2028TP-HTR-SIOM SYS-6028TP-HC1R-SIOM SYS-6028TP-HC0R-SIOM SYS-1029TP-DC0R SYS-1029TP-DC1R SYS-1029TP-DTR SYS-2029TP-HC0R SYS-2029TP-HC1R SYS-2029TP-HTR SYS-6029TP-HC0R SYS-6029TP-HC1R SYS-6029TP-HTR SYS-2029BT-HNC0R SYS-2029BT-HNC1R SYS-2029BT-HNR SYS-2029BT-HNTR SYS-2029BT-HTR SYS-6029BT-HNC0R AS -2123BT-HNC0R AS -2123BT-HTR 1028TP-DC1R 1028TP-DTR 2028BT-HNTR+
RSC-R1UU-2E8 	UIO	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	1026T-6RF+ SYS-1026T-6RFT+ 6016T-6RFT+ 6016T-NTF 6016T-NTRF 6016T-NTRF4+ 5016i-NTF 6016T-6RF+ 6016T-NT
RSC-R1UU-2U 	UIO	1U	LHS	Passive	Output: (2) UIO Signal: (2) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R1UU-E16 	UIO	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes, depending on MB gen3: No	Yes	No	No	No	No	6015A-NT
RSC-R1UU-E4R 	UIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x4	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R1UU-E8E16 	UIO	1U	LHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes, depending on MB gen3: Yes, depending on MB	Yes	No	No	No	Yes	6017B-NTF

RSC-R1UU-E8PR 	UIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R1UU-E8R+ 	UIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: No gen3: No	No	No	No	No	No	1026T-6RF+ SYS-1026T-6RFT+ 1026T-URF4+ 1026T-URF4+-LR SYS-5017C-URF 6016T-6RFT+ 6016T-NTRF4+ 6016T-URF4+ 1011M-Ni 1011M-UR 1016I-UF 5015B-NTB 5015B-NTRB 5015B-UB 5015B-URB 5015M-Ni 5015M-NTR 5015M-NT 5015M-UR 5015M-U 5016i-NTF 5016i-URF 6016T-6RF+
RSC-R1UU-UE16 	UIO	1U	LHS	Passive	Output: (1) PCI-E x16 (1) UIO Signal: (1) PCI-E x16 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: Yes, depending on MB	Yes	No	No	No	Yes	AS -1022G-URF 1026T-UF 1026T-URF 1026T-URF4+ 1026T-URF4+-LR 1027B-URF SYS-5017C-URF 6016T-UF 6016T-URF 6016T-URF4+ 6017B-URF 6016T-U
RSC-R1UU-UE8 	UIO	1U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	1026T-6RF+ SYS-1026T-6RFT+ 6016T-6RFT+ 6016T-NTF 6016T-NTRF 6016T-NTRF4+ 1011M-Ni 1011M-UR 5015B-NTB 5015B-NTRB 5015M-Ni 5015M-NTR 5015M-NT 5016i-NTF 6015B-Ni 6015B-NTR 6015B-NT 6015C-Ni 6015C-NTR 6015C-NT 6015W-Ni 015W-NTR 6015W-NT 6016T-6RF+ 6016T-NT
RSC-R1UW-2E16 	WIO	1U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	1027R-72BRFTP 1027R-72RFTP 1027R-N3RF 1027R-WRF SYS-1027R-WRF4+ SYS-1027R-WRFT+ 5017R-WRF 6017R-72RFTP SYS-6017R-N3RF4+ SYS-6017R-N3RFT+ SYS-6017R-NTF SYS-6017R-WRF SYS-1018R-WC0R SYS-1028R-TDW SYS-1028R-WC1R SYS-1028R-WC1RT SYS-1028R-WMR SYS-1028R-WMRT SYS-1028R-WTNR SYS-1028R-WTNRT SYS-1028R-WTR SYS-1028R-WTRT SYS-5018R-WR SYS-6018R-TD8 SYS-6018R-TDW SYS-6018R-WTR SYS-6018R-WTRT SYS-1028U-E1CR4+ SYS-1028U-E1CRTP+ SYS-1028U-TNR4T+ SYS-1028U-TNRT+ SYS-1028U-TNRTP+ SYS-1028U-TR4+ SYS-1028U-TR4T+ SYS-1028U-TRT+ SYS-1028UX-CR-LL1 SYS-1028UX-CR-LL2 SSG-6019P-ACR12L SYS-1029P-WT SYS-1029P-WTR SYS-1029P-WTRT SYS-6019P-WT SYS-6019P-WT8 SYS-6019P-WTR SYS-1029U-E1CR25M SYS-1029U-E1CR4 SYS-1029U-E1CR4T SYS-1029U-E1CRT SYS-1029U-E1CRTP SYS-1029U-E1CRTP2 SYS-1029U-TR25M SYS-1029U-TR4 SYS-1029U-TR4T SYS-1029U-TRT SYS-1029U-TRTP SYS-1029U-TRTP2 SYS-6019U-TN4R4T SYS-6019U-TN4RT SYS-6019U-TR25M SYS-6019U-TR4 SYS-6019U-TR4T SYS-6019U-TRT SYS-6019U-TRTP SYS-6019U-TRTP2 SYS-1019P-WTR SYS-5019P-WT SYS-5019P-WTR

											1028UX-TR4 1029UX-CR-LL
RSC-R1UW-E16 	WIO	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-6017R-TDT+ 6017R-TDT+
RSC-R1UW-E8R 	WIO	1U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	No	1027R-72BRFTP 1027R-72RFTP SYS-1027R-WRF4+ SYS-1027R-WRFT+ 5017R-WRF 6017R-72RFTP SYS-6017R-N3RF4+ SYS-6017R-N3RFT+ SYS-1028R-TDW SYS-2028U-TN24R4T+ SYS-2048U-RTR4 SYS-6018R-TDW SYS-6018R-TD8
RSC-R1UW-U 	WIO	1U	LHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	No	
RSC-R2U-2E8 	Standard	2U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R2U-A3E8+ 	Standard	2U	LHS	Active	Output: (3) PCI-E x8 Signal: (3) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R2U-E8 	Standard	2U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: No gen3: No	No	No	No	No	No	
RSC-R2UE-2E4R 	Standard	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x4	gen2: No gen3: No	No	No	No	No	No	
RSC-R2UF-2E8GR 	FatTwin	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-F627R2-RT+ F628R2-RTPT+ F628R2-RTPT+ F627R2-RT+
RSC-R2UF-E16R 	FatTwin	2U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	
RSC-R2UFF-2E16B 	FatTwin	2U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-F628G2-FC0+ SYS-F628G2-FC0PT+ SYS-F628G2-FT+ SYS-F628G2-FTPT+ SYS-F628G3-FC0+ SYS-F628G3-FC0PT+ SYS-F628G3-FT+ SYS-F628G3-FTPT+ F627G2-F73+ F627G2-F73PT+ F627G2-FT+ F627G2-FTPT+ F627G3-F73+ F627G3-F73PT+ F627G3-FT+ F627G3-FTPT+
RSC-R2UFF-E16A 	FatTwin	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	F627G2-F73+ F627G2-F73PT+ F627G2-FT+ F627G2-FTPT+ F627G3-F73+ F627G3-F73PT+ F627G3-FT+ F627G3-FTPT+
RSC-R2UG-2E16 	GPU	2U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	Yes	2026GT-TF 2026GT-TRF
RSC-R2UG-2E16-X9 	GPU	2U	LHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRF 2027GR-TRFT 2027GR-TSF
RSC-R2UG-2E16R-X9 	GPU	2U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRF SYS-2027GR-TRFH SYS-2027GR-TRFHT 2026GT-TF 2026GT-TRF 2026GT-TRF-FM407 2026GT-TRF-FM409 2026GT-TRF-FM475 2027GR-TRFT 2027GR-TSF
RSC-R2UG-2E4E8 	GPU	2U	LHS	Passive	Output: (3) PCI-E x16 Signal: (2) PCI-E x4 (1) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	Yes	2026GT-TF 2026GT-TRF 2026GT-TRF-FM407 2026GT-TRF-FM409

RSC-R2UG-A2E16-A 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRFH SYS-2027GR-TRFHT
RSC-R2UG-A2E16-B 	GPU	2U	LHS	Active	Output: (2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027GR-TRFH SYS-2027GR-TRFHT
RSC-R2UG-E16R-X9 	GPU	2U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	No	No	SYS-2027GR-TRF SYS-2027GR-TRFH SYS-2027GR-TRFHT SYS-2028GR-TRH SYS-2028GR-TR SYS-2028GR-TRHT SYS-2028GR-TRT 2026GT-TF 2026GT-TRF 2026GT-TRF-FM407 2026GT-TRF-FM409 2026GT-TRF-FM475 2027GR-TRFT 2027GR-TSF
RSC-R2UG-E8G-X9 	GPU	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-2027GR-TRF 2027GR-TRFT 2027GR-TSF
RSC-R2UG-UR-X9 	GPU	2U	RHS	Passive	Output: (1) UIO Signal: (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	No	
RSC-R2US-3E8R 	Standard	2U	LHS	Passive	Output: (3) PCI-E x8 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SSG-2027B-DE2R24L SSG-6037B-DE2R16L
RSC-R2UT-2E8R 	Twin	2U	RHS	Passive	Output: (2) PCI-E x16 Signal: (2) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	Yes	2026TT-DLIBQRf 2026TT-DLIBXRF 2026TT-DLRF 6026TT-D6IBQRF 6026TT-D6IBXF 026TT-HDIBQRF 6026TT-HDIBXRF 6026TT-HDTRF 2122TC-DL6RF4
RSC-R2UT-3E8R 	Twin	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-2027TR-D70FRF SYS-2027TR-D70QRF SYS-2027TR-D70RF SYS-6027TR-D70FRF SYS-6027TR-D70QRF SYS-6027TR-D70RF SYS-6027TR-D71FRF SYS-6027TR-D71QRF SYS-6027TR-D71RF SYS-6027TR-DTFRF SYS-6027TR-DTQRF SYS-6027TR-DTRF SYS-6028TR-D72R SYS-6028TR-DTR
RSC-R2UT-E16R 	Twin	2U	RHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	Yes	No	No	No	No	6026TT-GIBQRF 6026TT-GIBXRF 6026TT-GTRF
RSC-R2UT-E8E16R 	Twin	2U	RHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	6027TR-GTRF
RSC-R2UU-2E2E4R 	UIO	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (2) PCI-E x2 (1) PCI-E x4	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R2UU-2E4E8R 	UIO	2U	RHS	Passive	Output: (3) PCI-E x8 Signal: (2) PCI-E x4 (1) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	2026T-URF4+ 6026T-URF4+
RSC-R2UU-2E4R 	UIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x4	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-2E8 	UIO	2U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R2UU-2E8R 	UIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	2021M-UR+V 2021M-UR+B 6025W-URV 6025W-URB

RSC-R2UU-2U 	UIO	2U	LHS	Passive	Output: (2) UIO Signal: (2) UIO (PCI-E x8)	gen2: Yes, depending on slots gen3: No	No	No	No	No	No	
RSC-R2UU-3E8G 	UIO	2U	LHS	Passive	Output: (3) PCI-E x16 Signal: (3) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-A4E8+ 	UIO	2U	LHS	Active	Output: (4) PCI-E x8 Signal: (4) PCI-E x8	gen2: Yes gen3: No	No	No	No	No	No	
RSC-R2UU-E8E16 	UIO	2U	LHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UU-U2E4E8G 	UIO	2U	LHS	Passive	Output: (1) PCI-E x16 (2) PCI-E x8 (1) UIO Signal: (2) PCI-E x4 (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	6027B-URF 2026T-URF4+ 6026T-URF4+
RSC-R2UU-UA3E8+ 	UIO	2U	LHS	Active	Output: (3) PCI-E x8 (1) UIO Signal: (3) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: No	No	No	No	No	No	AS -2022G-URF 2022G-URF4+ 6026T-UR 6026T-URF
RSC-R2UU-UE8 	UIO	2U	LHS	Passive	Output: (1) PCI-E x8 (1) UIO Signal: (1) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes, depending on MB gen3: No	No	No	No	No	No	
RSC-R2UW+-2E16-2E8 	WIO	2U	LHS	Passive	Output: (2) PCI-E x16 (2) PCI-E x8 Signal: (2) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	No	Yes	SYS-2027R-N3RFT+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+
RSC-R2UW-2E4R 	WIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x4	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-R2UW-2E8E16 	WIO	2U	LHS	Passive	Output: (3) PCI-E x16 Signal: (1) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	6027R-72RFTP+ 2027R-72RFTP+
RSC-R2UW-2E8E16+ 	WIO	2U	LHS	Passive	Output: (2) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (2) PCI-E x8	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	SYS-6027R-CDNRT+ SYS-6027R-TDT+ SYS-6028R-TDWNR
RSC-R2UW-2E8R 	WIO	2U	RHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	2027R-72RFTP+ SYS-2027R-N3RFT+ 6027R-72RFTP+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+ SYS-6028R-WTR SYS-6028R-WTRT
RSC-R2UW-4E8 	WIO	2U	LHS	Passive	Output: (4) PCI-E x8 Signal: (4) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	2027R-WRF SYS-5027R-WRF SYS-6027R-N3RF SYS-6027R-WRF SYS-2027R-N3RFT+ SYS-6027R-N3RF4+ SYS-6027R-N3RFT+ SYS-6028R-WTR SYS-6028R-WTRT
RSC-R2UW-E8R-UP 	WIO	2U	RHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	No	Yes	SYS-5027R-WRF SYS-5028R-WR SYS-6027R-CDNRT+ SYS-6027R-TDT+ SYS-6028R-TDWNR
RSC-R2UW-U2E8 	WIO	2U	LHS	Passive	Output: (2) PCI-E x8 (1) UIO Signal: (2) PCI-E x8 (1) UIO (PCI-E x8)	gen2: Yes gen3: Yes	No	No	No	No	Yes	
RSC-RBL-E16 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	No	No	No	No	SBI-7127R-SH SBI-7427R-SH SBI-7426T-SH SBI-7126T-SH.SBI-7126T-SL
RSC-RBL-E16LP 	Super Blade	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: No	No	No	No	No	No	SBI-7427R-S2L SBI-7427R-S2L
												AS -1012G-MTF AS -1041A-T2F AS -1041M-T2+B 1042G-LTF AS -1042G-TF SYS-1017R-MTF

RSC-RR1U-E16 	Standard	1U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes, depending on MB gen3: Yes, depending on MB	No	No	No	No	Yes	SYS-1026T-M3 SYS-1027B-MTF SYS-5017R-MF SYS-5017R-MTF SYS-5017R-MTRF SYS-6016T-MR SYS-6016T-MT SYS-6016T-MTHF SYS-6016T-MTLF SYS-6016T-T SYS-6017B-MTF SYS-6017B-MTLF SYS-6017B-MTRF 6017R-TDAF SYS-6017R-TDF SYS-8016B-6F SYS-8016B-TF SYS-8016B-TLF SYS-8017R-7FT+ SYS-8017R-TF+ 1011M-T2 1041M-82 1041M-T2 1016I-M6F 1016T-M3FB 1018D-73MTF 1026T-T 1026T-TF 5015A-EHF 5016I-M6F 5016I-MT 5016I-MTF 5016I-MTH 5016I-MTHF 5016T-MRB 5016T-MRB-LN4 5016T-MTFB 5016T-TB 5017P-TF 5017P-TLN4F 5018D-MF 5018D-MTLN4F 5018D-MTRF 6016T-TF 6017R-TDLRF 8014T-T 8014T-TB 8015C-TB
RSC-RR1U-E8 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8	gen2: Yes, depending on MB gen3: Yes, depending on MB	No	No	No	No	Yes	1012C-MRF AS -1021M-T2+V SYS-1017C-TF SYS-1027R-73DARF 1027R-73DBRF SYS-5017C-LF SYS-5017C-MF SYS-5017C-MTF SYS-5017C-MTRF SYS-5017C-TF SYS-5037MC-H86RF SYS-5037MC-H8TRF 5037MR-H8TRF 6016T-6F SYS-6017R-TDF+ 1012A-M73RF 1012A-MRF 1012A-MTF 1015B-3B 1015B-M3B 1016I-TF 1025C-3B 1025C-M3B 1027R-73DAF 5015B-M3B 5016I-MR 5016I-MRF 5016I-MRH 5016I-MRHF 5016I-T 5016I-TF 5038ML-H8TRF 6015C-M3 6015C-M3B 6015C-MT 6015C-MT 6017R-M7RF 6017R-M7UF 6017R-MTLF SYS-5038MD-H8TRF SYS-5038ML-H8TRF SYS-5038MR-H8TRF SYS-6018R-MD SYS-6018R-MT SYS-6018R-MTR SYS-6018R-TD SYS-6018R-TDTP SYS-6018R-TDTPR SYS-5039MS-H8TRF
RSC-RR1U-HT 	Standard	1U	LHS	Passive	Output: (1) PCI-E x8 Signal: (1) PCI-E x8 + HT connector	gen2: No gen3: No	No	No	No	No	No	
RSC-U2N4-6 	Ultra	2U	LHS	Passive	Output: (1) PCI-E x16 Signal: (1) PCI-E x16	gen2: Yes gen3: Yes	No	4	No	Yes	Yes	SYS-2028U-TN24RT+
RSC-UN4-88 	Ultra	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (2) PCI-E x8	gen2: Yes gen3: Yes	No	4	No	Yes	Yes	SYS-1028U-TN10RT+
RSC-W-68 	WIO	1U	LHS	Passive	Output: (1) PCI-E x16 (1) PCI-E x8 Signal: (1) PCI-E x16 (1) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	Yes	No	SYS-5019S-WR
RSC-W-88 	WIO	1U	LHS	Passive	Output: (2) PCI-E x8 Signal: (8) PCI-E x8	gen2: Yes gen3: Yes	No	No	No	Yes	Yes	SYS-6028R-WTR SYS-1028R-WTR SYS-1028R-WC1R
RSC-W2-66					Output:							

	WIO	2U	LHS	Passive	(2) PCI-E x16 Signal: (2) PCI-E x16	gen2: Yes gen3: Yes	Yes	No	No	Yes	Yes	SYS-6028UX-TR4 SYS-2048U-RTR4

Terms & Conditions | Privacy | Investor Relations | Jobs | Site Map | Follow Us
SuperServer® | Motherboards | Chassis | SuperRack® | SuperBlade® | Embedded | Networking | Storage | Solu

Copyright © 2018 Super Micro Computer, Inc. Information in this document is subject to change without n
Other products and companies referred to herein are trademarks or registered trademarks of their respective companies or mark ho
Click for Logo Guidelines