




Right Angle DIN Plugs


171-1031-E, 171-1051-E, 171-1080-E, 171-1081-E

KOBICONN


Right Angle DIN Plugs



3 Pin
180 Arc
171-1031-E



5 Pin
180 Arc
171-1051-E



8 Pin
270 Arc
171-1080-E
171-1081-E

Dimensions: In.

SPECIFICATIONS

Type:	Right Angle DIN
Insulation Resistance:	100MΩ min @ 500VDC
Contact Resistance:	30mΩ max
Dielectric Strength:	250VAC for 1 Minute
RoHS Compliant	

MATERIALS

Color:	171-1031-E, 171-1051-E, 171-1081-E - Gray; 171-1080-E - Black
Sleeve:	Nickel Plated Steel
Body:	Polyethylene
Strain Relief:	PVC
Insulator:	ABS
Pins:	Nickel Plated Brass

Date Last Revised: 12-23-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300938

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-1081-E](#) [171-1031-E](#) [171-1051-E](#) [171-1080-E](#)