

3.3 V HCMOS/ TTL, J LEADED, PLASTIC MOLDED SURFACE MOUNT CRYSTAL CLOCK OSCILLATOR

ASML SERIES

RoHS
Compliant



14.0 x 8.95 x 4.7 mm

The 14x9.8mm plastic package oscillator is not recommended for new designs. Please consider our reduced size ceramic or plastic molded SMD packages. Recommended series include ASL, ASV, ASVM, ASFL, ASFLM, ASE, ASEM.

Product Life Cycle: Declining, Planned EOL/Obsolescence pending 12/31/2011

FEATURES:

- Industry standard J-Leaded terminals.
- Plastic molded SMD, suitable for RoHS compliant reflow
- Tristate Enable/Disable.
- HCMOS output.
- 3.3Vdc operation.
- Extended temperature -40°C to +85°C option.

APPLICATIONS:

- Provide clock signals for microprocessors and digital circuits.
- Communication equipment, AV and OA equipment

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range:		1.0	-----	106.25	MHz	
Operating Temperature:		0	-----	+70	°C	See options
Storage Temperature:		-55	-----	+125	°C	
Overall Frequency Stability*:		-100	-----	+100	ppm	See options
Supply Voltage (Vdd):		2.97	3.3	3.63	V	
Supply Current (I _{dd}):		-----	-----	15	mA	F ≤ 20 MHz
		-----	-----	35		F ≤ 70 MHz
		-----	-----	60		F ≤ 106.25 MHz
Output Load		-----	-----	15	pF	
		-----	-----	10	TTL	
Output Voltage:	V _{OH}	0.9*Vdd	-----	-----	V	
	V _{OL}	-----	-----	0.1*Vdd	V	
Tri-state function :		"1" (VIH≥2.2V) or Open: Oscillation "0" (VIL<0.8V) : Hi Z				
Aging:		-5.0	-----	+5.0	ppm	@+25°C First year
Symmetry:		40	-----	60	%	@1/2Vdd (See options)
Start-up Time :		-----	-----	10	ms	
Rise/Fall Time (Tr/Tf):		-----	-----	5	ns	
Period jitter one sigma :		-----	-----	25	ps	

OPTIONS AND PART IDENTIFICATION

(Left blank if standard)

ASML - MHz - - - -

Frequency in MHz
Please specify the frequency in MHz. e.g. 14.31818MHz

Operating Temp. Range
D: -10°C to +60°C
E: -20°C to +70°C
F: -30°C to +70°C
N: -30°C to +85°C
L: -40°C to +85°C

Overall Freq. Stability
R: ±25ppm
K: ±30ppm
C: ±50ppm

Symmetry
Blank: 40/60% @1/2Vdd
S: 45/55% @1/2Vdd
S1: 45/55% @1.4Vdc

Packaging
Blank: Bulk
T: 1000pcs/reel

