

NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: X100WBLK
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001" [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. P/N: X100WRED
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001" [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.


3. P/N: 9230
BODY & FITTINGS: BRASS. NICKEL PLATED.
PIN: BRASS. GOLD PLATED.
DIELECTRIC: PTFE.

4. P/N: 0480
HOUSING: MOLDED DELRIN. BLACK.

5. P/N: W-500/0
20AWG 105X40 TINNED COPPER
0.080 [2.03] O.D. PVC INSULATION

6. P/N: W-500/2
20AWG 105X40 TINNED COPPER
0.080 [2.03] O.D. PVC INSULATION

7. PERFORMANCE:
MAXIMUM CURRENT: 3.0 AMPS
MAXIMUM VOLTAGE: 1000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F [105°C]



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.					
		±	.XX ± .XXX ±	±			DESCRIPTION				
		MATERIAL			DRAWN		R.L.	9/10			
		SEE NOTE.			APPROVED BY						
		FINISH						BNC FEMALE (9230) ADAPTER TO MINI-HOOK'S (X100W)			
		SEE NOTE.									
NEXT ASSY	USED ON							SIZE	CODE IDENT NO.	DRAWING NO.	REV.
								B	08505	1001	
APPLICATION		DO NOT SCALE DRAWING						SCALE	1:1		SHEET 1 OF 1