

PGA / BGA / PLCC - PLCC SOLDER TAIL

<< Back To Search Results

Series
540



PGA / BGA / PLCC - PLCC solder tail
PLCC
Socket for Plastic Leaded Chip Carrier (PLCC),
Solder tail

PLCC sockets, solder tail, with precision stamped contacts providing component retention thanks to positive spring action.

Technical specs.:

Insulator:	Glass filled thermoplastic PPS-GF40-FR
Flammability:	UL 94V-O
Contact:	Phosphor bronze
Mechanical life:	Min. 25 cycles
Rated current:	1 A
Contact resistance:	Max. 30 m?
Dielectric strength:	Min. 500 V RMS
Insulation resistance:	Min. 1000 M?
Capacitance:	Max. 1 pF

Dimensions



Ordering information RoHS-compliant parts

PP Plating code Sleeve Clip
88 Tin Tin

General technical specs. ...

No of poles	A1/A2	B1/B2	C1/C2	D	E	Order Codes
28	18.09	7.62	11.2	22.12		540-88-028-24-008
32	18.04/20.06	7.62/10.16	11.2/13.6	23.12		540-88-032-24-008
44	23.1	12.7	16.2	29.12		540-88-044-24-008
52	25.7	15.24	18.8	32.85		540-88-052-24-008
68	30.8	20.32	23.7	39.9		540-88-068-24-008
84	35.95	25.4	28.9	47.4		540-88-084-24-008

- Home
- About Us
- Products
- Technical Assistance
- Distributors & Reps
- Distributors Login
- Contact Us
- Job Opportunities
- Newsletters

NEWS

[January 2010] **ARROW CENTRAL EUROPE** has been appointed as New Distributor Partner.
More >>

[January 2010] **New Sales and Marketing Director**