



Part Number: 98122-1006

Image not available

Status: Active - Custom
Series: [98122](#)
Category: Crimp Housings

Series image - Reference only

Mates With Part(s):
[98761](#)

Use With:
 Sicma 1.5 and 2.8mm female terminals from FCI

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC:

Low-Halogen Status: Not Reviewed

Part Detail

General

Status	Active - Custom
Category	Crimp Housings
Series	98122
Application	Power, Wire-to-Wire
Comments	The current is specified within the FCI Sicma terminal specification for 1.50mm and 2.80mm terminals.
Product Name	NSSC

Physical

Circuits (maximum)	30
Color - Resin	Black, Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Material Info

UPC	822348276158
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-98122-010
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application
Tooling**

[Check our list of old tooling that used to be available for this part](#)

