

19 Series


RoHS
Compliant

NYLON 6.6

GENERAL PURPOSE


MATERIAL OPERATING TEMPERATURE: -40°C to +85°C

APPLICATION OPERATING TEMPERATURE: -10°C to +85°C




Part Number	Width mm [Inch]	Length mm [Inch]	Max Bundle Diameter mm [Inch]	Min Loop Tensile Kg [lb]
I - 40lb				
19-I100	3.6 [.14]	100 [4.0]	22.6 [0.89]	18 [40]
S - 50lb				
19-S160	4.8 [.189]	160 [6.3]	41.9 [1.65]	22 [50]
19-S200	4.8 [.189]	200 [8.0]	54.8 [2.16]	22 [50]
19-S305	4.8 [.189]	305 [12.0]	88.1 [3.47]	22 [50]
19-S380	4.8 [.189]	380 [15.0]	111.0 [4.39]	22 [50]

PART NUMBER SYSTEM



N: Natural
B: Normal UV Black

C: 100PCS
Number: Other Quantity



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[19-I100B-C](#) [19-I100N-C](#) [19-S160B-C](#) [19-S160N-C](#) [19-S200B-C](#) [19-S200N-C](#) [19-S305B-C](#) [19-S305N-C](#) [19-S380B-C](#) [19-S380N-C](#)