




Shrink-Kon®



NOTES:

1. HEAVY WALL CROSS-LINKED POLYOLEFIN
2. ADHESIVE LINED
3. 3:1 SHRINK RATIO
4. CONTINUOUS OPERATING TEMPERATURE: -55°C TO 110°C
5. UL LISTED AND CSA CERTIFIED TO 600V, 90°C
6. MAXIMUM RATING 1kV, 90°C
7. SHRINK TEMPERATURE: 120°C
8. AVAILABLE COLORS: BLACK (STANDARD) OR RED (R SUFFIX)

CATALOG NUMBER	CABLE RANGE	Ø D EXPANDED	Ø d RECOVERED	W RECOVERED	STANDARD LENGTH
HS16-12 HS16-12L HS16-12-4	#16 - #12 AWG	.35	.12	.07	3 IN 6 IN 48 IN
HS12-6 HS12-6L HS12-6-4	#12 - #6 AWG	.51	.16	.08	3 IN 6 IN 48 IN
HS6-1 HS6-1L HS6-1-4	#6 - #1 AWG	.75	.24	.12	4 IN 8 IN 48 IN
HS4-30 HS4-30L HS4-30-4	#4 - 3/0 AWG	1.10	.35	.12	5 IN 9 IN 48 IN

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

*** SEE ERN (****)
FOR APPROVAL SIGNATURES
& RELEASE DATE.
PROJECT NO: ****

Thomas & Betts
www.tnb.com

DESCRIPTION:

**SHRINK-KON HEAVY WALL
HEAT SHRINK**

ORIGINAL PROJECT NO / (ERN NO)

TM401345 / (2010327)

SHEET NO:

1 OF 2

REV. NO:

**

DRAWING NO:

WSD-000473

THIS DRAWING IS INTENDED FOR DESCRIPTIVE PURPOSES ONLY. AND THE RIGHT IS RESERVED TO DEVIATE FROM ANY OF THE DETAILS SHOWN HEREON.

©2008 Thomas & Betts - Proprietary. All Rights Reserved

* NOT UL OR CSA LISTED

CATALOG NUMBER	CABLE RANGE	ØD EXPANDED	Ød RECOVERED	W RECOVERED	STANDARD LENGTH
HS40-400 HS40-400L HS40-400-4	4/0 - 400 MCM	1.50	.47	.14	8 IN 12 IN 48 IN
HS500-1000 HS500-1000L HS500-1000-4	500 - 1000 MCM	2.00	.63	.14	9 IN 15 IN 48 IN
HS12-30 HS30-30 HS30-4	800 - 1250 MCM	3.54	1.18	.15	12 IN 30 IN 48 IN
HS12-40 HS30-40 HS40-4-TB *	1500 - 2500 MCM	4.72	1.52	.15	12 IN 30 IN 48 IN

Thomas & Betts
www.tnb.com

DESCRIPTION:

**SHRINK-KON HEAVY WALL
HEAT SHRINK**

ORIGINAL PROJECT NO / (ERN NO)

TM401345 / (2010327)

SHEET NO:

2 OF 2

REV. NO:

DRAWING NO:

WSD-000473